



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TRAVELERC6

2 (C6) 3-prong connectors, in-line surge suppressor with 1 in/1 out tel/modem/ethernet combo

Highlights



- 120V / 240V compatible
- 306 joule
 - Two 3-prong (C6) connectors
- 1 in/1 out tel/modem/ethernet combo In-line design
- \$50,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's Traveler In-Line surge suppressor features a 306 joule rating to handle even the strongest surges. In-line design, over current protection and 120/240V compatibility make this surge suppressor ideal for notebook computers and PDAs. Integrated phone line protection allows you to safeguard tel/modem and AC connections with a single unit. "Protected" LED lets you instantly know whether your wall jacks have potentially damaging signals. \$50,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only).

Applications

- Ideal for notebook computers, PDAs or other electronics requiring AC and tel/modem safeguarding

Package Includes

- TRAVELERC6 surge suppressor
- Instruction manual with warranty information

Features

- In-line design places AC line surge protection between your notebook computer or PDAs' power adapter and the power cord leading to the wall outlet
- 120/240V compatibility operates on voltage worldwide, automatically switching between 120V or 240V AC power
- Surge suppression rating: 306 joules
- Includes two 3-prong (C6) connectors
- Built-in LED confirms suppressor "protection present" (green)
- 1 line in/ 1 line out tel/modem/ethernet combo
- Single small push-button switch activates overcurrent detection circuit
- \$50,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only) covers connected equipment

Specifications

OVERVIEW	
Intended Application	Home/Office, Travel
OUTPUT	
Frequency compatibility	50 / 60 Hz

Outlet quantity / type	2 (C6) 3-prong connectors
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Recommended Electrical Service	120V (110-125V), 230V (220-250V)
Input connection type	Two 3-prong (C6) connectors
Input cord length details	In-line
Voltage compatibility (VAC)	120; 230
Maximum Surge Amps	12000
LEDS ALARMS & SWITCHES	
Switches	Single small push-button switch activates over-current detection circuit
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green)
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	306
AC suppression response time	< 1 ns
Clamping voltage (RMS)	150
UL1449 let through rating	900V
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	Yes
PHYSICAL	
Unit Dimensions (HWD/in)	1.75 x 4.25 x 1
Unit Dimensions (HWD/cm)	4.4 x 10.8 x 2.5
Shipping Dimensions (HWD/in)	9 x 7 x 1.2
Shipping Dimensions (HWD/cm)	22.9 x 17.8 x 3
Unit weight (lbs)	0.2
Unit weight (kg)	0.1
Material of construction	Plastic
Style	In-Line
Form factors supported	In-line
SPECIAL FEATURES	
Appearance	Ultra-compact portable in-line protector in an attractive, all black lightweight enclosure

CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Approvals	UL1950
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2638.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.