















Identification	Part number	Drawing	Dimensions in mm
<p>Coding system with code pins</p> <p>standard </p> <p>Han-Modular® </p>	<p>09 30 000 9901¹⁾</p> <p>09 14 000 9901¹⁾</p>	<p>for hoods/housings with one insert/one frame</p>  <p>for hoods/housings with the inserts/two frames</p>  <p>• Code pin ○ Normal mounting screw</p> <p>M - Male insert F - Female insert</p>	
<p>Coding system with guide pins/bushes</p> <p>standard</p> <p>Guide pin </p> <p>Guide bushing </p> <p>Han-Modular®</p> <p>Guide pin </p> <p>Guide bushing </p>	<p>09 33 000 9908¹⁾</p> <p>09 33 000 9909¹⁾</p> <p>09 14 000 9908¹⁾</p> <p>09 14 000 9909¹⁾</p>	<p>This system is used to guard against angled coupling and decoupling of the connector. The maximum permitted angle according to DIN EN 175 301-801 is $\pm 5^\circ$ (longitudinally).</p>  <p>for hoods/housings with one insert/one frame</p>  <p>for hoods/housings with the inserts/two frames</p>  <p>• Guide pin ○ Bush + Normal mounting screw</p> <p>M - Male insert F - Female insert</p>	
<p>Coding pins</p> <p>for Han E®, Han® EE, Han® Q 5/0, Han® Q 8/0 </p> <p>for Han D®, Han DD® with loss of contact </p>	<p>09 33 000 9954</p> <p>09 33 000 9915</p>	<p>Use of the coding pin prevents incorrect mating to other connectors of the same type. The male pin should be omitted from the opposing cavity in the male insert.</p> 	

¹⁾ Order 4 pieces for one connector