

Features

- Suitable for HARTING SC contacts
- For GI-Fibre 50 - 62.5 / 125µm
- Using of guiding pins (male and female) is recommended (see chapter 40).

Technical characteristics

Approvals




Inserts

Number of contacts	4
Insertion loss	< 0.5 dB
Material	polycarbonate
Limiting temperatures	-40 °C ... +85 °C
Flammability acc. to UL 94	V 0
Mechanical working life - mating cycles	≥ 500

Assembly instructions

Male insert (09 14 004 4701)




A Assemble the SC contact

Push the SC contact from the side into the relevant insert (1)
Push the fixing plate from the side over the contacts (2)

B SC contact fixed in the module

Female insert (09 14 004 4711)



A Assemble the SC contact

Push the centering ferrule (included in delivery) on the SC contact (1)
Push the SC contact from the side into the relevant insert (2)
Push the fixing plate from the side over the contacts (3)

B SC contact fixed in the module