






Number of contacts

64 +

Han
D/DD

Inserts

Identification	Series	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately (see Technical characteristics on page 02.04) 	Han D®	09 21 064 3001	09 21 064 3101	 1) Distance for contact max. 21 mm Contact arrangement view from termination side 	
Wrap terminal 1 x 1 mm 		09 21 064 2601	09 21 064 2701	Panel cut out for inserts for use without hoods/housings 	
Coding pin 			09 33 000 9915	Coding pin  Use of the coding pin prevents incorrect mating to other connectors of the same type. The male pin should be omitted from the opposing cavity in the male insert.	

Stock items in bold type