



## ***AL1012ULXPD8, AL1012ULXPD8CB*** ***Multi-Output Power Supply/Chargers***

Rev. DSAL1012ULXPD8 - J18G



### **Overview**

- These multi-output power supply/chargers convert a 115VAC/60Hz input to eight (8) 12VDC outputs.

#### ***AL1012ULXPD8***

- Fuse protected non-power limited outputs rated @ 3.5 amp each.

#### ***AL1012ULXPD8CB***

- Class 2 Rated PTC protected power limited outputs rated @ 2.5 amp each.

### **Specifications**

- 12VDC outputs.
- 10 amp of continuous supply current.
- Eight (8) protected outputs.
- Input 115VAC / 60Hz, 1.9 amp.
- Input fuse rated @ 3.5 amp/250V.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.
- Built-in charger for sealed lead acid or gel type batteries.
- Maximum charge current .7 amp.
- Automatic switch over to stand-by battery when AC fails (zero voltage drop).
- AC fail supervision (form "C" contacts).
- Low battery supervision (form "C" contacts).
- Battery presence supervision (form "C" contacts).
- AC input and DC output LED indicators.
- Enclosure:
  - Combination knockouts are 1/2" and 3/4"
  - Accommodates one (1) 12VDC/12AH battery.

### **Agency Approvals**



UL 294 UL Listed for Access Control System Units.



CUL Listed - CSA Standard C22.2 No.205-M1983, Signal Equipment.

**Enclosure Dimensions**

15.5"H x 12"W x 4.5"D

