



HARTING RJ Industrial® 10G RJ45 bulkhead

RJ45
RJ Industrial

Advantages

- Compact and robust design
- 360° shielding
- Compatible with HIFF dimensions for use in the Han® 3 A series with the Han® 3 A HIFF adapter 09 45 515 0024 or in the PushPull series with the HARTING PushPull Compact bulkhead mounting housing 09 45 545 0028 or the HARTING PushPull EasyInstall bulkhead mounting housing 09 45 545 0032

Technical characteristics

Mating face	RJ45 acc. to IEC 60 603-7
Number of contacts	8
Transmission category	Cat. 6, performance class E _A , suitable for 1/10 Gigabit Ethernet
Degree of protection	IP 20
Mating cycles	min. 750
Temperature range	-40 °C ... +70 °C
Housing material	Zinc die-cast, nickel-plated
Flammability acc. to UL 94	V-0

Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------

HARTING RJ Industrial® 10G
RJ45 bulkhead

09 45 545 1560

