




Product information G 20 KW 3 F 3m

Industrial Connecting Solutions:Rectangular Connectors:DIN VDE 0627 / IEC 61984 Connectors (G serie):Cable socket:G 20 KW 3 F 3m

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-24347-24348-37699/en/conf/ui/state>

Name	G 20 KW 3 F 3m
	
	Cable socket, with integrally molded lead
Delivery informations	
Availability	available
Product description	
Description	Cable socket, with integrally molded lead
Type	G 20 KW 3 F 3m
Order No.	932 041-002
Type of contact	forked spring
Number of contacts	2 + PE
Cable material	PVC
Cable length	3 m
Conductor size	3 x 1 mm ²
Cable type	H05 VV-F 3G1
Standard	DIN VDE 0627 / IEC 61984
Housing Color	grey
Technical data	
Rated voltage	AC/DC 250 V
Rated current	10 A
Contact resistance	<= 4 mOhm
Material	
Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 65
Pollution severity	3
Temperature range	-40 °C to +90 °C
Inflammability class	
Housing	94 HB
Contact bearer	94 HB
Approvals	
VDE	VDE
Packaging unit	
Packaging unit	20 pieces
Scope of delivery and accessories	
Scope of delivery	1 cable socket with integrally molded lead, 1 central screw M 3 x 18, 1 gasket
Accessories to order separately	can be plugged into G 30 E 3 M, G 20 KW 3 M 1,5m



HIRSCHMANN


A BELDEN BRAND

Industrial Connecting Solutions:Rectangular Connectors:DIN VDE 0627 / IEC 61984 Connectors (G serie):Cable socket:G 20 KW 3 F 3m

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-24347-24348-37699/en/conf/ui/state>

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2

58579 Schalksmühle

Germany

Phone: +49 7127/14-1806

E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.