



Product information Compact OpenRail unmanaged Fast Ethernet switch 8-24 ports, without fiber ports - RS20-1600T1T1SDAUHH

Industrial Ethernet:Entry Level Hubs And Switches:Configurable Unmanaged Switches:Fast Ethernet switches:Compact OpenRail unmanaged Fast Ethernet switch 8-24 ports, without fiber ports

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49855-50104-80728-80578/en/RS20-1600T1T1SDAUHH/ui/state>

Name	Compact OpenRail unmanaged Fast Ethernet switch 8-24 ports, without fiber ports
	
	16 port Fast-Ethernet-Switch, unmanaged, for DIN rail store-and-forward-switching, fanless design
Delivery informations	
Availability	available
Product description	
Description	16 port Fast-Ethernet-Switch, unmanaged, for DIN rail store-and-forward-switching, fanless design
Port type and quantity	16 ports in total; 1. uplink: 10/100BASE-TX, RJ45; 2. uplink: 10/100BASE-TX, RJ45; 14 x standard 10/100 BASE TX, RJ45
Type	RS20-1600T1T1SDAUHH
Order No.	943 434-047
More Interfaces	
Power supply/signaling contact	1 x plug-in terminal block, 6-pin
Network size - length of cable	
Twisted pair (TP)	0 m ... 100 m
Network size - cascading	
Line - / star topology	Any
Power requirements	
Operating voltage	12/24/48 V DC (9,6-60) V and 24 V AC (18-30) V (redundant)
Current consumption at 24 V DC	392
Current consumption at 48 V DC	196
Power output in Btu (IT) h	32.1
Ambient conditions	
Operating temperature	0 °C ... 60 °C
Storage/transport temperature	-40 °C ... 70 °C
Relative humidity (non-condensing)	10 % ... 95 %
MTBF	45.5 years (MIL-HDBK-217F)
Protective paint on PCB	No
Mechanical construction	
Dimensions (W x H x D)	110 mm x 131 mm x 111 mm
Mounting	DIN Rail
Weight	600 g
Protection class	IP20
Mechanical stability	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	1 mm, 2 Hz - 13.2 Hz, 90 min.; 0.7g, 13.2 Hz - 100 Hz, 90 min.; 3.5 mm, 3 Hz - 9 Hz, 10 cycles, 1 octave/min.; 1g, 9 Hz - 150 Hz, 10 cycles, 1 octave/min.
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	6 kV contact discharge, 8kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80 - 1000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage	power line: 2kV (line/earth), 1kV (line/line), 1kV data line
EN 61000-4-6 conducted immunity	3 V (10 kHz - 150 kHz), 10 V (150 kHz - 80 MHz)
EMC emitted immunity	
FCC CFR47 Part 15	FCC CFR47 Part 15
EN 55022	EN 55022 Class A
Approvals	
Safety of industrial control equipment	cUL 508

Industrial Ethernet:Entry Level Hubs And Switches:Configurable Unmanaged Switches:Fast Ethernet switches:Compact OpenRail unmanaged Fast Ethernet switch 8-24 ports, without fiber ports
<http://www.e-catalog.beldensolutions.com/link/57078-24455-49855-50104-80728-80578/en/RS20-1600T1T1SDAUHH/uistate>

Hazardous locations	cUL 1604 Class1 Div 2
Germanischer Lloyd	-
Railway norm	-
Substation	-
Scope of delivery and accessories	
Scope of delivery	Device, terminal block, operating manual

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.