



SAFETY DATA SHEET Swarfega Orange

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name Swarfega Orange
Product No. SOR15L, SOR2LC, SOR400MP, SOR41BEN, SOR45L, SOR49UFR, SOR4LCSFX, SOR531ES, SOR55BCE, SOR55PES, SOR56SFR, SOR8419EX, SOR92BSC, SOR92RCE, SOR94JSC, 6025, SOR4LMP, SOR2LTPC, SORC4LTRPC, SOR610, SOR620, SOR440, SOR445, SOR115, SOR200, 1452, 1454, sor4ltr, SOR400MPSC, SOR400MPNL

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Hand cleaner.

1.3. Details of the supplier of the safety data sheet

Supplier Deb Ltd
Denby Hall Way
Denby
Derbyshire
DE5 8JZ
Main Tel. 01773 855100
Technical Tel 01773 855105
reach@deb.co.uk

1.4. Emergency telephone number

National Poisons Information Service (UK) 0844 8920111

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (1999/45/EEC) Not classified.

2.2. Label elements

Risk Phrases

NC Not classified.

Safety Phrases

NC Not classified.

2.3. Other hazards

This product does not contain any PBT or vPvB substances.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

Swarfega Orange

INCI

Aqua
Polyethylene
Trideceth-8
Glycerin
Limonene
2-Bromo-2-Nitropropane-1, 3-Diol
BHT
Methylisothiazolinone
Methylchloroisothiazolinone
Magnesium Nitrate
Magnesium Chloride
Parfum
Sodium Carbomer
Triticum Vulgare
Titanium Dioxide
Tetrasodium EDTA
CI 16035
CI 19140

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation

Not relevant Unlikely route of exposure as the product does not contain volatile substances.

Ingestion

Rinse mouth thoroughly. Get medical attention if any discomfort continues.

Skin contact

Not relevant

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention promptly if symptoms occur after washing.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation.

No specific symptoms noted.

Ingestion

No specific symptoms noted.

Skin contact

None under normal conditions.

Eye contact

May cause temporary eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

No specific first aid measures noted.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products

No hazardous decomposition products.

5.3. Advice for firefighters

Swarfega Orange

Special Fire Fighting Procedures

No specific fire fighting procedure given.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with eyes.

6.2. Environmental precautions

Not relevant considering the small amounts used.

6.3. Methods and material for containment and cleaning up

Flush away small spillages with plenty of water. Do not let washing down water contaminate ponds or waterways. Large quantities should not be discharged into the drain but removed with absorbing material.

6.4. Reference to other sections

For waste disposal, see section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Avoid contact with eyes.

7.2. Conditions for safe storage, including any incompatibilities

Store in closed original container at temperatures between 0°C and 40°C.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Ingredient Comments

No exposure limits noted for ingredient(s).

8.2. Exposure controls

Engineering measures

Not relevant

Respiratory equipment

No specific recommendations.

Eye protection

Wear eye protection if there is a risk of this product getting in the eyes.

Hygiene measures

Not relevant

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Viscous liquid.
Colour	Orange.
Odour	Orange.
pH-Value, Conc. Solution	7.0-8.0

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

No specific reactivity hazards associated with this product.

10.2. Chemical stability

Swarfega Orange

Stable under normal temperature conditions.

[10.3. Possibility of hazardous reactions](#)

None known.

[10.4. Conditions to avoid](#)

There are no known conditions that are likely to result in a hazardous situation.

[10.5. Incompatible materials](#)

Materials To Avoid

No incompatible groups noted.

[10.6. Hazardous decomposition products](#)

None under normal conditions.

SECTION 11: TOXICOLOGICAL INFORMATION

[11.1. Information on toxicological effects](#)

Inhalation

No specific health warnings noted.

Ingestion

May cause discomfort if swallowed.

Skin contact

Skin irritation is not anticipated when used normally.

Eye contact

May cause temporary eye irritation.

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Not regarded as dangerous for the environment.

[12.1. Toxicity](#)

Acute Fish Toxicity

Not considered toxic to fish.

[12.2. Persistence and degradability](#)

Degradability

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

[12.3. Bioaccumulative potential](#)

Bioaccumulative potential

No data available on bioaccumulation.

[12.4. Mobility in soil](#)

Mobility:

The product is soluble in water.

[12.5. Results of PBT and vPvB assessment](#)

This product does not contain any PBT or vPvB substances.

[12.6. Other adverse effects](#)

Swarfega Orange

None known.

SECTION 13: DISPOSAL CONSIDERATIONS

General information

When handling waste, consideration should be made to the safety precautions applying to handling of the product.

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

Road Transport Notes Not Classified

Rail Transport Notes Not classified.

Sea Transport Notes Not classified.

Air Transport Notes Not classified.

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

Not applicable.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU Legislation

This is a cosmetic product regulated by Directive 76/768 EEC (as amended) & Regulation EC no 1223/2009 (as amended) and is thus exempt from the Safety Data Sheet requirements of Regulation EC no 453/2010. It is also exempt from the classification and labelling rules of the Dangerous Preparations Directive 1999/45/EC and the Classification, Labelling and Packaging Regulation (EC) No 1272/2008.

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION

Revision Comments

Revision of information

Revision Date 21/04/2011

Revision 5

Supersedes date 15/02/2011

Swarfega Orange

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in a process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.