


## Product information

### Industrial HiVision - Industrial HiVision 4.2, 25 Nodes

Industrial Ethernet:Archive - Industrial Ethernet:Network Management (Archive):Industrial HiVision (Archive):Industrial HiVision

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49814-103324-103325-176891/en/IHV-025F04.2/uistate>

Name	Industrial HiVision
	
	Network management software for monitoring of industrial networks with up to 25 nodes (IP addresses).
<b>Delivery informations</b>	
Availability	available
<b>Product description</b>	
Description	Network management software for monitoring of industrial networks with up to 25 nodes (IP addresses).
Type	Industrial HiVision 4.2, 25 Nodes
Order No.	943 156-025
License	License enables supervision of up to 25 nodes (IP addresses).
Node extension	To increase the amount of supervised nodes, licenses can be combined.
<b>Diagnostics</b>	
Topology recognition	Topology recognition is based on LLDP (Link Layer Discovery Protocol, IEEE802.1AB) and Learned Address Tables. Switches, routers, WLAN devices, unmanaged switches/hubs, and end devices are supported. Can also map networks behind a router. Path Availability Calculation.
Monitoring	Graphical status representation for devices, links, power supplies, fans, and any other device sub-component. Status displays for third-party products. All statuses are configurable. Supports multiple topology windows and a network hierarchy view. User configurable event log. Customisable event actions.
Modules and components	MACH 4000/1000/100, MICE, PowerMICE, RS2, EAGLE20, RS20/30/40, RSR, RSB, MICE20/30, OCTOPUS, LION, GigaLION, BAT54 Access Point and Client, BAT300, SPIDER, any third-party SNMP capable device, any ICMP (Ping) capable device.
Event generation	polling and SNMPv1 trap support
Alarm and event actions	alarm and event logging. Alarm actions such as message window, email, SMS and start executable.
<b>SCADA /Process visualisation</b>	
OPC Server	Map device and connection states as well as device properties. Can be used inside SCADA systems via the OPC Data Access 2.0/3.0 interface.
ActiveX Control	Graphical User Interface can be reused inside SCADA systems via an ActiveX control
<b>Protocols</b>	
Supported protocols	HiDiscovery, ICMP (Ping), SNMPv1, SNMPv3, OPC DA 2.0/3.0
<b>Configuration</b>	
Configuration functions	Individual device configuration. Configuration of multiple devices simultaneously. Configuration of identical parameters across multiple device types simultaneously. Firmware update of multiple devices.
<b>Documentation</b>	
Documentation	documentation, export of maps and lists, inventory
<b>Language Support</b>	
Menus and dialogs	English, French, Spanish, Chinese, Japanese, Korean, German, Greek
Manual and help texts	English, German
<b>Software requirements</b>	
Operating system	Windows XP Professional Edition (32 Bit), Windows 7 Professional / Ultimate (32 Bit), Windows Vista Business / Ultimate (32 Bit), Windows 2003 Server (32 Bit) (with limitations), Windows 2008 Server (32 Bit) (with limitations), Windows 2008 Server R2 (64 Bit) (with limitations), PC Linux 32 Bit: Kernel 2.6, glibc 2.4, PC Linux 64 Bit: Kernel 2.6, glibc 2.4 (approved for Debian 5.0)
Browser	Internet Explorer 4.0 or higher, Java runtime environment 1.5.0 is also installed
<b>Hardware requirements</b>	
Processor	x86 compatible CPU, min. 1 GHz
RAM	1 GB, 2 GB recommended
Hard disk space	300 MB free
Network	Ethernet network with TCP/IP protocol stack. Supports multiple network cards.
<b>Scope of delivery and accessories</b>	
Scope of delivery	printed manual (German and English), CD-ROM with multilingual product version, manual and form for licensing.

Industrial Ethernet:Archive - Industrial Ethernet:Network Management (Archive):Industrial HiVision (Archive):Industrial HiVision

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49814-103324-103325-176891/en/IHV-025F04.2/ui/state>

#### Product variants

##### Version + Nodes

Full version - nodes.

For more information please contact:

**Hirschmann Automation and Control GmbH**

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: [inet-sales@belden.com](mailto:inet-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.