

Product information

MACH102-24TP-F

Industrial Ethernet: Workgroup Switches: Fast-/Gigabit Ethernet Workgroup Switches, 10/24 ports :MACH102-24TP-F

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49848-85612-40984/en/conf/ui.state>

Name		MACH102-24TP-F
		
		26 port Fast Ethernet/Gigabit Ethernet Industrial Workgroup Switch (2 x GE, 24 x FE), managed, Software Layer 2 Professional, Store-and-Forward-Switching, fanless Design
Delivery informations		
Availability		available
Product description		
Description		26 port Fast Ethernet/Gigabit Ethernet Industrial Workgroup Switch (2 x GE, 24 x FE), managed, Software Layer 2 Professional, Store-and-Forward-Switching, fanless Design
Port type and quantity		26 ports in total; 24x (10/100 BASE-TX, RJ45) and 2 Gigabit Combo ports
Type		MACH102-24TP-F
Order No.		943 969-401
More Interfaces		
Power supply/signaling contact		1 x plug-in terminal block, 2-pin, output manual or automatic switchable (max. 1 A, 24 V DC bzw. 24 V AC)
V.24 interface		1 x RJ11 socket, serial interface for device configuration
USB interface		1 x to connect auto-configuration adapter ACA21-USB
Network size - length of cable		
Twisted pair (TP)		0 - 100m
Multimode fiber (MM) 50/125 µm		Fast Ethernet: cf. SFP LWL module M-FAST SFP-MM/LC; Gigabit Ethernet: cf. SFP LWL module M-SFP-SX/LC and M-SFP-LX/LC
Multimode fiber (MM) 62.5/125 µm		Fast Ethernet: cf. SFP LWL module M-FAST SFP-MM/LC; Gigabit Ethernet: cf. SFP LWL module M-SFP-SX/LC and M-SFP-LX/LC
Single mode fiber (SM) 9/125 µm		Fast Ethernet: cf. SFP LWL module M-FAST SFP-SM/LC and M-FAST SFP-SM+/LC; Gigabit Ethernet: cf. SFP LWL module M-SFP-LX/LC
Single mode fiber (LH) 9/125 µm (long haul transceiver)		Fast Ethernet: cf. SFP LWL modul M-FAST SFP-LH/LC; Gigabit Ethernet: cf. SFP LWL modul M-SFP-LH/LC and M-SFP-LH+/LC
Network size - cascability		
Line - / star topology		any
Ring structure (HIPER-Ring) quantity switches		50 (reconfiguration time < 0,3 sec.)
Power requirements		
Operating voltage		100 - 240 VAC, 47 - 63 Hz
Power output in Btu (IT) h		55
Rated current		0.4 - 0.2 A
Power consumption		16 W
Software		
Management		serial Interface, web interface, SNMP V1/V2, HiVision file transfer SW HTTP/TFTP
Diagnostics		LEDs, log-file, syslog, signal contact, RMON (statistic, history, alarms, events), port mirroring, topology discovery 802.1AB, cable diagnostic
Configuration		Comand line interface (CLI), TELNET, BootP, DHCP, DHCP option 82, HiDiscovery, auto-configuration adapter (ACD11, ACA21-USB), Watchdog configuration; integrated DHCP server
Security		Port security (IP and MAC), SNMP V3, SSH, authentication (802.1x)
Redundancy functions		HIPER-ring (ring structure), MRP (IEC-ring functionality), RSTP 802.1D-2004, redundant network/ring coupling, dual homing, link aggregation
Filter		QoS 4 Klassen, Portpriorisierung (IEEE 802.1D/p), VLAN (IEEE 802.1Q), shared VLAN learning, Multicast (IGMP Snooping/Querier), Multicast Detection unknown Multicast, Broadcastlimiter, Fast Aging, Multicast GMRP IEEE 802.1D
Industrial Profiles		EtherNet/IP, PROFINET, configuration and diagnostic via automation software tools like e.g. STEP7, or Control Logix
Time synchronisation		SNTP server, realtime clock with energy buffer
Flow control		Flow Control 802.3x, Port Priority 802.1D/p, Priority (TOS/DIFFSERV), Prio (MAC/IP), Prio Mapping (TOS Layer2), Traffic Shaping (Unicast, Multicast, Broadcast) Ingress / Egress
Ambient conditions		
Operating temperature		0° - +50°C
Storage/transport temperature		-20° - +85°C

Industrial Ethernet: Workgroup Switches: Fast-/Gigabit Ethernet Workgroup Switches, 10/24 ports : MACH102-24TP-F
<http://www.e-catalog.beldensolutions.com/link/57078-24455-49848-85612-40984/en/conf/ui.state>

Relative humidity (non-condensing)	10% to 95%
MTBF	13.26 years (MIL-HDBK-217F Gb 25°C)
Mechanical construction	
Dimensions (W x H x D)	448 x 44 x 310 (without fixing bracket)
Mounting	19" control cabinet
Weight	3.85 kg
Protection class	IP20
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80 - 2700 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 4 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line), 4 kV data line
EN 61000-4-6 conducted immunity	10 V (150 kHz - 80 MHz)
EMC emitted immunity	
FCC CFR47 Part 15	FCC 47 CFR Part 15 Class A
EN 55022	EN 55022 Class A
Approvals	
Safety of industrial control equipment	cUL 508
Safety of information technology equipment	cUL 60950-1
Scope of delivery and accessories	
Scope of delivery	MACH100 device, terminal block for signal contact, 2 brackets with fasteningscrews (pre-assembled), housing feet - stick-on, non-heating appliance cable - Euro model, CD-ROM with user manual, installation user manual
Accessories to order separately	Fast Ethernet SFP modules, Gigabit Ethernet SFP modules, autoConfiguration Adapter ACA21-USB, terminal cable, Industrial Hivision Network Management software

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.