



SAFETY DATA SHEET
COLD GALVANISING SPRAY - HOT DIP FINISH

Page: 1

Compilation date: 22/11/2012

Revision No: 3

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: COLD GALVANISING SPRAY - HOT DIP FINISH

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Metal galvanising spray

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: F+: R12; -: R52/53

Most important adverse effects: Extremely flammable. Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements

Label elements under CHIP:

Hazard symbols: Extremely flammable.



Risk phrases: R12: Extremely flammable.

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases: S38: In case of insufficient ventilation, wear suitable respiratory equipment.

Precautionary phrases: Pressurized container: protect from sunlight and do not expose to temperatures

[cont...]

SAFETY DATA SHEET

COLD GALVANISING SPRAY - HOT DIP FINISH

Page: 2

exceeding 50°C. Do not pierce or burn, even after use.

Do not spray on a naked flame or any incandescent material. Keep away from sources of ignition - No smoking. Keep out of the reach of children.

2.3. Other hazards

PBT: This substance is not identified as a PBT substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE)

EINECS	CAS	CHIP Classification	CLP Classification	Percent
270-704-2	68476-85-7	F+: R12 Substance with a Community workplace exposure limit.	-	50-70%

XYLENE

215-535-7	1330-20-7	-: R10; Xn: R20/21; Xi: R38	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Skin Irrit. 2: H315	10-30%
-----------	-----------	-----------------------------	--	--------

SOLVENT NAPHTHA (PETROLEUM), LIGHT AROMATIC

265-199-0	64742-95-6	-: R10; Xi: R37; N: R51/53; Xn: R65; -: R66; -: R67	-	1-10%
-----------	------------	---	---	-------

AROMATIC HYDROCARBON

-	64742-95-6	Xn: R65; -: R10; Xi: R37; N: R51/53; -: R66; -: R67	-	1-10%
---	------------	---	---	-------

ALUMINIUM POWDER

231-072-3	-	-: R10; -: R15 Substance with a Community workplace exposure limit.	-	1-10%
-----------	---	--	---	-------

HYDROGENATED HYDROCARBON

265-150-3	64742-48-9	Xn: R65; -: R66 Substance with a Community workplace exposure limit.	-	1-10%
-----------	------------	---	---	-------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

[cont...]

SAFETY DATA SHEET

COLD GALVANISING SPRAY - HOT DIP FINISH

Page: 3

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Do not use water. Alcohol resistant foam. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Extremely flammable. Forms explosive air-vapour mixture. In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Do not use equipment in clean-up procedure which may produce sparks. Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Smoking is forbidden.

[cont...]

SAFETY DATA SHEET

COLD GALVANISING SPRAY - HOT DIP FINISH

Page: 4

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep away from sources of ignition. Keep away from direct sunlight. Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE)

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1000ppm 1750mg/m3	1250ppm 2180mg/m3	-	-

XYLENE

UK	220 mg/m3	441 mg/m3	-	-
----	-----------	-----------	---	---

ALUMINIUM POWDER

UK	-	-	4mg/m3	-
----	---	---	--------	---

HYDROGENATED HYDROCARBON

UK	1000 MG/M3	-	-	-
----	------------	---	---	---

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Respiratory protection not normally required.

Hand protection: Protective gloves.

Eye protection: Safety glasses with side-shields.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Aerosol

Colour: Pale grey

Odour: Characteristic odour

Evaporation rate: Fast

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Not miscible

Viscosity: Non-viscous

Boiling point/range°C: -25

Melting point/range°C: < 0

Flammability limits %: lower: 3.4

[cont...]

SAFETY DATA SHEET

COLD GALVANISING SPRAY - HOT DIP FINISH

Page: 5

Flash point°C: < -40
Vapour pressure: 490
upper: 18
Autoflammability°C: > 300
Relative density: 1.4

9.2. Other information

Other information: Not applicable.

Section 10: Stability and reactivity

10.1. Reactivity

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

10.4. Conditions to avoid

Conditions to avoid: Direct sunlight. Heat. Sources of ignition.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: Not applicable.

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: Not applicable.

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

[cont...]

SAFETY DATA SHEET

COLD GALVANISING SPRAY - HOT DIP FINISH

Page: 6

12.4. Mobility in soil

Mobility: Highly volatile. Heavier than air.

12.5. Results of PBT and vPvB assessment

PBT identification: This substance is not identified as a PBT substance.

12.6. Other adverse effects

Other adverse effects: Very toxic to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1950

14.2. UN proper shipping name

Shipping name: AEROSOLS

14.3. Transport hazard class(es)

Transport class: 2

14.4. Packing group

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: EC Directive 94/1/EC adapting some technicalities of Council Directive 75/324/EEC on the approximation of the laws of Member States relating to aerosol dispensers.

This safety data sheet is prepared in accordance with Commission Regulation (EU) No

[cont...]

SAFETY DATA SHEET

COLD GALVANISING SPRAY - HOT DIP FINISH

Page: 7

453/2010.

Compiled in accordance with REACH.

Phrases used in s.2 and 3: H226: Flammable liquid and vapour.

H312: Harmful in contact with skin.

H315: Causes skin irritation.

H332: Harmful if inhaled.

R10: Flammable.

R12: Extremely flammable.

R15: Contact with water liberates extremely flammable gases.

R20/21: Harmful by inhalation and in contact with skin.

R37: Irritating to respiratory system.

R38: Irritating to skin.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65: Harmful: may cause lung damage if swallowed.

R66: Repeated exposure may cause skin dryness or cracking.

R67: Vapours may cause drowsiness and dizziness.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.