




Product information M-FAST SFP-SM/LC EEC

Industrial Ethernet: System Accessories: Fiberoptic Transceiver: SFP Fast-Ethernet Transceiver for media module: M-FAST SFP-SM/LC EEC

<http://www.e-catalog.beldensolutions.com/link/57078-24455-24544-24535-24528-40590/en/conf/ui/state>

Name	M-FAST SFP-SM/LC EEC
	
	SFP Fiberoptic Fast-Ethernet Transceiver
Delivery informations	
Availability	available
Product description	
Description	SFP Fiberoptic Fast-Ethernet Transceiver
Port type and quantity	1 x 100 BASE-FX with LC connector
Type	M-FAST SFP-SM/LC EEC
Order No.	943 946-001
Network size - length of cable	
Multimode fiber (MM) 50/125 µm	-
Multimode fiber (MM) 62.5/125 µm	-
Single mode fiber (SM) 9/125 µm	0 - 25 km 0 - 13 dB link budget bei 1310nm A = 0.4 dB/km, 3 dB Reserve, B = 800 MHz x km
Single mode fiber (LH) 9/125 µm (long haul transceiver)	-
Power requirements	
Operating voltage	power supply via the switch
Power consumption	1 W
Service	
Diagnostics	optical input- and output power, transceiver temperature
Ambient conditions	
Operating temperature	-40 °C to +85 °C
Storage/transport temperature	-40°C to +85°C
Relative humidity (non-condensing)	10% to 95%
MTBF	652 years; Telcordia SR-332
Mechanical construction	
Dimensions (W x H x D)	20 mm x 18 mm x 50 mm
Mounting	SFP slot
Weight	40 g
Protection class	IP 20
Mechanical stability	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	1 mm, 2 Hz - 13,2 Hz, 90 min.; 0,7g, 13,2 Hz - 100 Hz, 90 min.; 3,5 mm, 3 Hz - 9 Hz, 10 cycles, 1 octave/min.; 1g, 9 Hz - 150 Hz, 10 cycles, 1 octave/min.
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	6 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80 - 1000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line), 1kV data line
EN 61000-4-6 conducted immunity	3 V (10 kHz - 150 kHz), 10 V (150 kHz - 80 MHz)
EMC emitted immunity	
FCC CFR47 Part 15	FCC CFR47 Part 15 Class A
EN 55022	EN 55022 Class A
Approvals	
Safety of information technology equipment	cUL 60950-1
Shipbuilding	Germanischer Lloyd, ABS, BV, DNV, LR, KR, RINA

Industrial Ethernet: System Accessories: Fiberoptic Transceiver: SFP Fast-Ethernet Transceiver for media module: M-FAST SFP-SM/LC EEC

<http://www.e-catalog.beldensolutions.com/link/57078-24455-24544-24535-24528-40590/en/conf/uistate>

Scope of delivery and accessories

Scope of delivery	-
Accessories to order separately	SFP module

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.