

FLEXIBLE POLYOLEFIN

2 : 1 Shrink

MILITARY SPECIFICATION and UL / CSA



RoHS Compliant

TYPICAL FEATURES

- | | |
|--|---|
| <p>1) SUMITUBE B2 is a very flexible, flame-retarded, radiation-crosslinked heat shrinkable polyolefin tubing which meets all of the material and functional requirements of Military Specification AMS-DTL- 23053/5, Class 1 and Class 3.</p> <p>2) Shrink temperature is 90°C.</p> | <p>3) Operating temperature range is -55°C to +135°C and up to 200°C for short time durations.</p> <p>4) B2 is recommended for use in general purpose applications such as wire marking, color coding, and electrical insulation of light wire harness assemblies. For higher expansion ratio versions see B2(3X), B2(4X), and B2(4XC) data sheets.</p> |
|--|---|

STANDARD SIZES

SIZE	INSIDE DIAMETER AS SUPPLIED (MIN)		INSIDE DIAMETER AFTER RECOVERY (MAX)		WALL THICKNESS AFTER RECOVERY (NOM)	
	INCH	(MM)	INCH	(MM)	INCH	(MM)
3/64	.046	1.2	.023	0.6	.016	0.40
1/16	.063	1.6	.031	0.8	.017	0.43
3/32	.093	2.4	.046	1.2	.020	0.51
1/8	.125	3.2	.062	1.6	.020	0.51
3/16	.187	4.8	.093	2.4	.020	0.51
1/4	.250	6.4	.125	3.2	.025	0.64
3/8	.375	9.5	.187	4.8	.025	0.64
1/2	.500	12.7	.250	6.4	.025	0.64
5/8*	.625	15.9	.313	7.9	.027	0.69
3/4	.750	19.1	.375	9.5	.030	0.76
1	1.000	25.4	.500	12.7	.035	0.89
1 1/4*	1.250	31.8	.625	15.9	.038	0.97
1 1/2	1.500	38.1	.750	19.1	.040	1.02
2	2.000	50.8	1.000	25.4	.045	1.14
3	3.000	76.2	1.500	38.1	.050	1.27
4	4.000	101.6	2.000	50.8	.055	1.40

Standard Colors: Black, White, Red, Yellow, Blue, Green, Violet, Gray, Orange (Other colors subject to factory approval and quote)

Standard Package: Spooled (S) or 4 foot lengths (4')

How to Order: (Type of material) (Size) (Color) (Packaging)
Example: B2 1/4 Black 4'

* non - SAE spec sizes

B2 SPECIFICATION VALUES

PROPERTY (UNITS)	TEST METHOD	REQUIREMENT
Physical: Tensile strength (psi) Elongation (%) Specific gravity Low temperature flex (-55° C) Heat shock (250° C, 4 hrs.) Heat resistance (175° C, 168 hrs.) Elongation (%) Secant modulus (psi) Longitudinal change (%)	ASTM D638 ASTM D638 ASTM D792 AMS-DTL-23053 AMS-DTL-23053 ASTM D638 ASTM D882 AMS-DTL-23053	1500 min. 200 min. 1.35 max. no cracking no cracking 100 min. 2.5 X 10 ⁴ max. ±5
Electrical: Dielectric strength (volts/mil) Volume resistivity (ohm-cm)	ASTM D876 ASTM D876	500 min. 1.0 X 10 ¹⁴ min.
Chemical: Corrosion (175° C, 16 hrs.) Water absorption (%) Fluid resistance (23° C, 24 hrs.) Tensile strength (psi) Flammability Shrink temperature, nominal	AMS-DTL-23053 ASTM D570 AMS-DTL-23053 UL 224 VW-1	no corrosion 0.5 max. 1000 min. pass 90° C

Specification references: AMS-DTL-23053/5, Class 1 and Class 3.
 UL 224 125° C, 600 V, VW-1 File E48762 YDPU2
 CSA C22.2 No. 198.1-98


SUMITOMO ELECTRIC
INTERCONNECT PRODUCTS INC.
www.seipusa.com

915 Armorlite Drive
 San Marcos, CA 92069

Telephone: (800) 758-3515
 FAX: (800) 758-3517

Rev. 2/28/07