



SAFETY DATA SHEET
PIPE SEALANT WITH PTFE

Page: 1

Compilation date: 23/09/2011

Revision No: 2

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: PIPE SEALANT WITH PTFE

Product code: 301285

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Pipe Sealant

1.3. Details of the supplier of the safety data sheet

Company name: Anixter Limited

Anixter Ltd

3 Edmund Road

Sheffield

S2 4EB

Tel: 01709 361616

Fax: 01709 362825

Email: gregg.walker@anixter.com

1.4. Emergency telephone number

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: Xi: R36/37/38; Sens.: R43

Most important adverse effects: Irritating to eyes, respiratory system and skin. May cause sensitisation by skin contact.

2.2. Label elements

Label elements under CHIP:

Hazard symbols: Irritant.



Risk phrases: R36/37/38: Irritating to eyes, respiratory system and skin.

R43: May cause sensitisation by skin contact.

Safety phrases: S2: Keep out of the reach of children.

S23: Do not breathe fumes.

S24/25: Avoid contact with skin and eyes.

S37/39: Wear suitable gloves and eye / face protection.

S46: If swallowed, seek medical advice immediately and show this container or label.

[cont...]

SAFETY DATA SHEET

PIPE SEALANT WITH PTFE

Page: 2

2.3. Other hazards

PBT: This substance is not identified as a PBT substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

METHACRYLIC DIESTER OF POLYETHYLENE GLYCOL

EINECS	CAS	CHIP Classification	CLP Classification	Percent
-	25852-47-5	Xi: R36/37/38	-	10-30%

3-[2-(METHACRYLOYLOXY)ETHOXYCARBONYL]PROPIONIC ACID

244-096-4	20882-04-6	Xi: R36/37/38	-	<1%
-----------	------------	---------------	---	-----

SILICON DIOXIDE

-	7631-86-9	Xn: R20	-	<1%
---	-----------	---------	---	-----

2-HYDROXYETHYL METHACRYLATE

212-782-2	868-77-9	Xi: R36/38; Sens.: R43	Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317	<1%
-----------	----------	------------------------	--	-----

ETHYLENE GLYCOL

203-473-3	107-21-1	Xn: R22	Acute Tox. 4: H302	<1%
-----------	----------	---------	--------------------	-----

CUMENE HYDROPEROXIDE

201-524-7	80-15-9	O: R7; Xn: R21/22; T: R23; C: R34; Xn: R48/20/22; N: R51/53	Org. Perox. EF: H242; Acute Tox. 3: H331; Acute Tox. 4: H312; Acute Tox. 4: H302; STOT RE 2: H373; Skin Corr. 1B: H314	<1%
-----------	---------	--	---	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

[cont...]

SAFETY DATA SHEET

PIPE SEALANT WITH PTFE

Page: 3

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

[cont...]

SAFETY DATA SHEET

PIPE SEALANT WITH PTFE

Page: 4

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: Not applicable.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Yellow

Odour: Perceptible odour

Solubility in water: Insoluble

Kinematic viscosity: 80000 mPas

Viscosity test method: Kinematic viscosity in 10⁻⁶ m²/s at 40°C (ISO 3104/3105)

Vapour pressure: <0.5 mmHg@25C

Relative density: 1.15

9.2. Other information

Other information: Not applicable.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

[cont...]

SAFETY DATA SHEET

PIPE SEALANT WITH PTFE

Page: 5

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Relevant effects for mixture:

Effect	Route	Basis
Irritation	OPT INH DRM	Hazardous: calculated
Sensitisation	DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: Not applicable.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This substance is not identified as a PBT substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

[cont...]

SAFETY DATA SHEET

PIPE SEALANT WITH PTFE

Page: 6

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and 3: H242: Heating may cause a fire.

H302: Harmful if swallowed.

H312: Harmful in contact with skin.

H314: Causes severe skin burns and eye damage.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H331: Toxic if inhaled.

H373: May cause damage to organs <or state all organs affected, if known> through prolonged or repeated exposure <state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>.

R7: May cause fire.

R20: Harmful by inhalation.

R21/22: Harmful in contact with skin and if swallowed.

R22: Harmful if swallowed.

R23: Toxic by inhalation.

R34: Causes burns.

R36/37/38: Irritating to eyes, respiratory system and skin.

[cont...]

SAFETY DATA SHEET
PIPE SEALANT WITH PTFE

Page: 7

R36/38: Irritating to eyes and skin.

R43: May cause sensitisation by skin contact.

R48/20/22: Harmful: danger of serious damage to health by prolonged exposure through inhalation and if swallowed.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.