




## Product information MM4-4TX/SFP

Industrial Ethernet:Modular Industrial Switches:Media modules:Gigabit Ethernet MICE media modules:MM4-4TX/SFP

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49860-81778-24484-40334/en/conf/ui/state>

Name	MM4-4TX/SFP
	
	Media module for MICE Switch MS4128,10/100/1000BASE-TX und 1000BASE-SX/LX
<b>Delivery informations</b>	
Availability	available
<b>Product description</b>	
Description	Media module for MICE Switch MS4128, 10/100/1000BASE-TX und 1000BASE-SX/LX
Port type and quantity	4 x 1000BASE-fiber with SFP modules, or 4 x 10/100/1000BASE-TX, TP cable, RJ45-sockets, autocrossing, autoneg., autopolarity, any combination TX or SFP, 1 SFP deactivates 1TX, up to 4 ports
Type	MM4-4TX/SFP
Order No.	943 010-001
<b>Network size - length of cable</b>	
Twisted pair (TP)	0 - 100 m
Multimode fiber (MM) 50/125 µm	cf. SFP module M-SFP-SX/LC and M-SFP-LX/LC
Multimode fiber (MM) 62.5/125 µm	cf. SFP module M-SFP-SX/LC and M-SFP-LX/LC
Single mode fiber (SM) 9/125 µm	cf. SFP module M-SFP-LX/LC
Single mode fiber (LH) 9/125 µm (long haul transceiver)	cf. SFP FO module M-SFP-LH/LC and M-SFP-LH+/LC
<b>Power requirements</b>	
Operating voltage	power supply via the backplane of the MICE switch
Power consumption	2 W
<b>Service</b>	
Diagnostics	LEDs (power, link status, data, 1000 Mbit/s, auto-negotiation, full duplex, ring port, LED test)
<b>Ambient conditions</b>	
Operating temperature	0 °C bis +60 °C standart ( optional -40°C to +70°C)
Storage/transport temperature	-40 °C to +70 °C
Protective paint on PCB	optional
Relative humidity (non-condensing)	10% to 95%
MTBF	163 years; MIL-HDBK 217F: Gb 25 °C
<b>Mechanical construction</b>	
Dimensions (W x H x D)	38 mm x 134 mm x 118 mm
Mounting	Backplane
Weight	180 g
Protection class	IP 20
<b>Mechanical stability</b>	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	1 mm, 2 Hz - 13.2 Hz, 90 min.; 0.7g, 13.2 Hz - 100 Hz, 90 min.; 3.5 mm, 3 Hz - 9 Hz, 10 cycles, 1 octave/min.; 1g, 9 Hz - 150 Hz, 10 cycles, 1 octave/min.
<b>EMC interference immunity</b>	
EN 61000-4-2 electrostatic discharge (ESD)	6 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80 - 1000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line), 1kV data line
EN 61000-4-6 conducted immunity	3 V (10 kHz - 150 kHz), 10 V (150 kHz - 80 MHz)
<b>EMC emitted immunity</b>	
FCC CFR47 Part 15	FCC CFR47 Part 15 Class A
EN 55022	EN 55022 Class A



# HIRSCHMANN

A **BELDEN** BRAND

Industrial Ethernet:Modular Industrial Switches:Media modules:Gigabit Ethernet MICE media modules:MM4-4TX/SFP

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49860-81778-24484-40334/en/conf/uistate>

#### Approvals

Safety of industrial control equipment	cUL 508
Hazardous locations	cUL 1604 Class1 Div 2
Shipbuilding	Germanischer Lloyd
Railway norm	optional
Substation	optional

#### Scope of delivery and accessories

Scope of delivery	module, operating manual
Accessories to order separately	ML-MS2/MM labels

For more information please contact:

**Hirschmann Automation and Control GmbH**

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: [inet-sales@belden.com](mailto:inet-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.