

Product information

G 30 KW 3 M 2m

Industrial Connecting Solutions: Rectangular Connectors: DIN VDE 0627 / IEC 61984 Connectors (G series): Cable plug: G 30 KW 3 M 2m

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-24347-24349-36964/en/conf/ui/state>


Name	
G 30 KW 3 M 2m	
	
Cable plug with integrally molded lead	
Delivery informations	
Availability	available
Product description	
Description	Cable plug with integrally molded lead
Type	G 30 KW 3 M 2m
Order No.	931 783-001
Type of contact	blade contacts
Number of contacts	3 + PE
Cable material	PVC
Cable length	2 m
Conductor size	4 x 0.75 mm ²
Cable type	A03 VV-F 4G0,75
Standard	DIN VDE 0627 / IEC 61984
Housing Color	grey
Technical data	
Pin dimensions	2.8 mm x 0.8 mm
Rated voltage	AC/DC 250 V
Rated current	10 A
Contact resistance	<= 4 mOhm
Mounting	central screw
Material	
Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 65
Pollution severity	3
Temperature range	-40 °C to +90 °C
Inflammability class	
Housing	94 HB
Contact bearer	94 HB
Approvals	
VDE	VDE
Packing unit	
Packaging unit	20 pieces
Scope of delivery and accessories	
Scope of delivery	1 cable plug with integrally molded lead
Accessories to order separately	can be plugged into G 30 E 3 F grau/grey, G 30 W 3 F grau/grey, G 30 KW 3 F 2m

Industrial Connecting Solutions: Rectangular Connectors: DIN VDE 0627 / IEC 61984 Connectors (G serie): Cable plug: G 30 KW 3 M 2m

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-24347-24349-36964/en/conf/ui/STATE>

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.