

Product information GML 209 NJ LED 24 HH grau/grey

Industrial Connecting Solutions:Rectangular Connectors:Valve Connectors (Type A -B -C):Type B:Field Attachable Valve Connectors:Valve Connectors with electronic insert (Industrial standard):GML 209

NJ LED 24 HH grau/grey

Name	GML 209 NJ LED 24 HH grau/grey

	function indicator (LED) with protective circuit (diode)
Delivery informations	
Availability	available
Product description	
Description	function indicator (LED) with protective circuit (diode)
Туре	GML 209 NJ LED 24 HH graw/grey
Order No.	933 389-106
Other standard types	transparent housing, locking screw black: Order No. 933 389-100
Number of contacts	2 + PE
Cable gland	PG 9 (grey)
Conductor size	max. 1.5 mm ²
Standard	industrial standard (11 mm)
Housing Color	transparent
Construction type	В
Description of Wiring	
LED color	LED red
Suppressor	diode
Other characteristics	correct polarity must be ensured
Technical data	
Pin dimensions	6.3 mm x 0.8 mm
Rated voltage	DC 24 V
Rated current	8 A
Contact resistance	<= 4 m0hm
Type of termination	screw / cable shoe / cable eye
Suitable cables	4.5 mm to 7 mm diameter
Mounting	central screw
Material	
Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 65
Pollution severity	3
Temperature range	-40 °C to +90 °C
Inflammability class	
Housing	94 V-1
Contact bearer	94 HB
Approvals	
UR	UR
VDE	VDE
Packing unit	
Packaging unit	50 pieces





Industrial Connecting Solutions: Rectangular Connectors: Valve Connectors (Type A -B -C): Type B: Field Attachable Valve Connectors: Valve Connectors with electronic insert (Industrial standard): GML 209

NJ LED 24 HH grau/grey

http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-256266-256271-276218-24327-35250/en/conf/uistate

Scope of delivery and accessories

Accessories to order separately
(NBR) flat gasket GM 207-3, Order No. 731 423-002; knurled screw GDM 3011-8, Order No. 732 574-001; stainless steel screw GDM 3011 RF-1, Order No. 734 363-001

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2 58579 Schalksmühle Germany

Phone: +49 7127/14-1806 E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.

