


Product information

BAT54-Rail Client

Industrial Ethernet:Archive - Industrial Ethernet:Industrial Wireless LAN:Chassis:BAT54-Rail Client

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49814-49859-24497-40939/en/conf/ui/state>

Name		BAT54-Rail Client
		
		Dualband industrial Wireless LAN access point/client with one radio module with IEEE 802.11a/b/g/h/i/replaced by order number: 943 926-521
Delivery informations		
Availability		not available
Product description		
Description		Dualband industrial Wireless LAN access point/client with one radio module with IEEE 802.11a/b/g/h/i replaced by order number: 943 926-521
Port type and quantity		1 x WLAN interface, one LAN port 10/100 BASE-TX, autosensing, Power over Ethernet according to IEEE 802.3af
Type		BAT54-Rail Client
Order No.		943 926-501
Radio technology		
Antenna connector		2 x RP-SMA jack antenna connectors
Range		Up to 20 km with external antenna (depending on type of antenna, frequency range and data rate)
Frequency band		1 x radio module, 2.4 GHz and 5 GHz: 2400-2483.5 MHz (ISM) and 5170-5810 MHz
Modulation		22M0F7D(DSSS/OFDM) @ 2.4 GHz 20M0G7D (OFDM) @ 5 GHz
Radio topology		WLAN access client-, client-bridge-modus, fixed mesh with RSTP
Power requirements		
Operating voltage		2 x DC 24 V; DC 12 V external power supply (230 V) 1 x Power over Ethernet according to IEEE802.3af; all power supplies redundant to each other
Current consumption at 24 V DC		417 mA
Current consumption		DC 12 V: 625 mA; DC 24 V: 417 mA; PoE (48 V DC): 167 mA
Ambient conditions		
Operation temperature		-30 °C to +50 °C
Storage/transport temperature		-40 °C to +70 °C
Relative humidity (non-condensing)		max. 95%
MTBF		43.3 years
Mechanical construction		
Dimensions (W x H x D)		80 mm x 100 mm x 135 mm
Mounting		for wall and Din Rail mounting
Protection class		IP 40
Approvals		
Safety of information technology equipment		EN 60950
Radio		EN 300328, EN 301893, notified in all countries of EU. For other notifications or certifications please refer to INET-Sales@hirschmann.de
Environmental		EN 61000-6-2, EN 61131 for operation in automation environment EMC approval for E1 certification (cars and vehicles) available
Scope of delivery and accessories		
Scope of delivery		Device, CD, serial cable, Ethernet cable (3 m), 2 x 3-dBi-Dipol - Dualband antennas, 1 x 50 Ohm terminators, Rail mount material
Accessories to order separately		External antennas for 802.11b/g and 802.11a/h operation; adapter cable and surge arrestor



HIRSCHMANN

A **BELDEN** BRAND

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.