

Product information

OZD Profi 12M G12-1300 EEC PRO

Fiber Interfaces:Fieldbus Repeater:Profibus LWL-Repeater:OZD Profi 12M G12-1300 EEC PRO

<http://www.e-catalog.beldensolutions.com/link/57078-57141-57128-57129-40421/en/conf/ui/state>

Name	OZD Profi 12M G12-1300 EEC PRO
	
	interface converter electrical/optical for PROFIBUS-field bus networks; repeater function; for quartz glass F0; long-haul version;extended temperature and humidity range
Delivery informations	
Availability	available
Product description	
Description	interface converter electrical/optical for PROFIBUS-field bus networks; repeater function; for quartz glass F0; long-haul version; extended temperature and humidity range
Port type and quantity	2 x optical: 4 sockets BFOC 2.5 (STR); 1 x electrical: Sub-D 9-pin, female, pin assignment according to EN 50170 part 1
Type	OZD Profi 12M G12-1300 EEC PRO
Order No.	943 908-321
Electrical interface	
Signal type	PROFIBUS (DP-V0, DP-V1, DP-V2 und FMS)
Bit rate	9.6; 19.2; 45.45; 93.75; 187.5; 500 kbit/s; 1.5; 3; 6; 12 Mbit/s (automatic setting)
Signal delay time (optional input/output)	<= 6.5 bit times
Input/output signal	RS 485 level
Input voltage range	-7 V ... +12 V
Galvanic isolation	no
Optical interface	
Wavelength	1310 nm
Cascadability	not limited
More interfaces	
Power supply	5-pin terminal block, screw mounting
Signaling contact	5-pin terminal block, screw mounting
Measuring outputs "Optical input power"	3-pin terminal block, screw mounting
Network size - length of cable	
Single mode fiber (SM) 9/125 µm	15000 m 10 dB link budget at 1310 nm; A = 0.5 dB/km, 2 dB reserve
Multimode fiber (MM) 50/125 µm	10000 m 12 dB link budget at 1310 nm; A = 1 dB/km, 2 dB reserve
Multimode fiber (MM) 62.5/125 µm	10000 m 12 dB link budget at 1310 nm; A = 1 dB/km, 2 dB reserve
Multimode fiber HCS (MM) 200/230 µm	-
Multimode fiber POF (MM) 980/1000 µm	-
Power requirements	
Operating voltage	18 ... 32 VDC, typ. 24 VDC
Galvanic isolation	yes
Current consumption	max. 200 mA
Power consumption	4.8 W
Output voltage/output current (pin6)	5 VDC +5%, -10%, short circuit-proof/90 mA
Redundancy	
Redundancy functions	HIPER-Ring (ring structure), redundant 24 V infeed
Ambient conditions	
Operating temperature	-20 °C to +60 °C
Storage/transport temperature	-40 °C to +70 °C



HIRSCHMANN

A BELDEN BRAND

Fiber Interfaces:Fieldbus Repeater:Profibus LWL-Repeater:OZD Profi 12M G12-1300 EEC PRO

<http://www.e-catalog.beldensolutions.com/link/57078-57141-57128-57129-40421/en/conf/ui/state>

Relative humidity	100% (condensing)
Mechanical construction	
Dimensions (W x H x D)	35 x 163 x 119 mm
Mounting	DIN rail
Weight	200 g
Protection class	IP 20
Housing material	plastics
Approvals	
Safety of information technology equipment	cUL 508
Hazardous locations	cUL 1604 Class1 Div 2; ATEX 100a, Zone 2
Issued or requested approvals	C-Tick
Scope of delivery and accessories	
Scope of delivery	device, start-up instructions
Accessories to order separately	manual, order no. 039 690-001

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.