




Product information OZD Profi G12DE ATEX 1

Fiber Interfaces:Fieldbus Repeater:Profibus LWL-Repeater:OZD Profi G12DE ATEX 1

<http://www.e-catalog.beldensolutions.com/link/57078-57141-57128-57129-39993/en/conf/ui/state>

Name	OZD Profi G12DE ATEX 1
	
	Interface converter electrical/optical for PROFIBUS networks; repeater function; in stainless steel cabinet; approvals for protection zones 1,21, 2 and 22
Delivery informations	
Availability	available
Product description	
Description	Interface converter electrical/optical for PROFIBUS networks; repeater function; in stainless steel cabinet; approvals for protection zones 1,21, 2 and 22
Port type and quantity	2 x optical: 4 sockets BFOC 2.5 (STR); 1 x electrical: Ex-e single clamp
Type	OZD Profi G12DE ATEX 1
Order No.	943 883-321
Electrical interface	
Signal type	PROFIBUS (DP-V0, DP-V1, DP-V2 und FMS)
Bit rate	9,6; 19,2; 45,45; 93,75; 187,5; 500 kbit/s; 1,5; 3; 6; 12 Mbit/s (automatic setting)
Signal delay time (optional input/output)	<= 6.5 bit times
Input/output signal	RS 485 level
Input voltage range	-7 V ... +12 V
Galvanic isolation	no
Optical interface	
Wavelength	860 nm
Cascadability	not limited
More Interfaces	
Power supply	Ex-e single clamp
Signaling contact	Ex-e single clamp
Measuring outputs "Optical input power"	Ex-e single clamp
Network size - length of cable	
Multimode fiber (MM) 50/125 µm	3000 m 13 dB link budget at 860 nm; A = 3 dB/km, 3 dB reserve
Multimode fiber (MM) 62.5/125 µm	3000 m 15 dB link budget at 860 nm; A = 3.5 dB/km, 3 dB reserve
Power requirements	
Operating voltage	18 ... 32 VDC, typ. 24 VDC
Galvanic isolation	yes
Current consumption	max. 200 mA
Power consumption	4.8 W
Output voltage/output current (pin6)	5 VDC +5%, -10%, short circuit-proof/90 mA
Redundancy	
Redundancy functions	HIPER-Ring (ring structure), redundant 24 V infeed
Ambient conditions	
Operating temperature	-20 °C to +55 °C
Storage/transport temperature	-40 °C to +80 °C
Relative humidity	10% to 100%
Mechanical construction	
Dimensions (W x H x D)	230 x 219 x 108 mm
Mounting	screw mounting on the mounting plate
Weight	3.7kg
Protection class	IP 66

Fiber Interfaces:Fieldbus Repeater:Profibus LWL-Repeater:OZD Profi G12DE ATEX 1

<http://www.e-catalog.beldensolutions.com/link/57078-57141-57128-57129-39993/en/conf/ui/state>

Housing material	stainless steel
Approvals	
Hazardous locations	ATEX 100a, Zone 2
Issued or requested approvals	C-Tick, According to EN 60079-28: Inherently safe optical radiation
Scope of delivery and accessories	
Scope of delivery	device, start-up instructions
Accessories to order separately	manual

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.