

## Product information

### RPS 120 EEC

Fiber Interfaces:Archive - Fiber Interfaces:Accessories Fiber Interfaces:DIN Rail Power Supplies:RPS 120 EEC

<http://www.e-catalog.beldensolutions.com/link/57078-57141-57328-57139-24574-40294/en/conf/uistate>

Name	RPS 120 EEC
	
	24 V DC DIN rail power supply unit
<b>Delivery informations</b>	
Availability	available
<b>Product description</b>	
Description	24 V DC DIN rail power supply unit
Type	RPS 120 EEC
Order No.	943 662-120
<b>More Interfaces</b>	
Voltage input	1 Bi-stable, quick-connect spring clamp terminals, 3-pin
Voltage output	1 Bi-stable, quick-connect spring clamp terminals, 6-pin
<b>Power requirements</b>	
Operating voltage	230 V
<b>Input data</b>	
230 V	100-240 V AC (-15/+10%); 50-60Hz or 110 to 300 V DC (+/-20%)
<b>Current consumption</b>	
230 V	max. 1,4-0,65 A at 100-240 V AC max. 1,2 - 0,45 A bei 120 - 300 V DC
Activation current	< 15 A at 100 and 230 V AC
<b>Output data</b>	
Output voltage	24-28 V DC (typ. 24,1 V); externally adjustable
<b>Output current</b>	
230 V	min. 5 - 4,5 A continuous 7,5 - 6,7 A for typ. 4 sec
<b>Service</b>	
Diagnostics	LED (DC OK, Overload)
<b>Redundancy</b>	
Redundancy functions	Power supply units can be connected in parallel
<b>Ambient conditions</b>	
Operating temperature	-25 °C to +70 °C (ab 60 °C Derating)
Storage/transport temperature	-40 °C to +85 °C
Relative humidity (non-condensing)	5 to 95 %
MTBF	-
<b>Mechanical construction</b>	
Dimensions (W x H x D)	40 mm x 124 mm x 117 mm
Mounting	DIN Rail 35 mm
Weight	620 g
Protection class	IP 20
<b>EMC interference immunity</b>	
EN 50082-1	EN 61000-6-1
EN 50082-2	EN 61000-6-2 (includes EN 55024)
<b>EMC emitted immunity</b>	
EN 50081-1	EN 61000-3-2, 61000-3-3, 61000-6-3, 61000-6-4
EN 50081-2	-

Fiber Interfaces:Archive - Fiber Interfaces:Accessories Fiber Interfaces:DIN Rail Power Supplies:RPS 120 EEC

<http://www.e-catalog.beldensolutions.com/link/57078-57141-57328-57139-24574-40294/en/conf/uistate>

**Scope of delivery and accessories**

<b>Scope of delivery</b>	Rail power supply, Description and operating manual
--------------------------	--

For more information please contact:

**Hirschmann Automation and Control GmbH**

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: [inet-sales@belden.com](mailto:inet-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.