

**HIRSCHMANN**A **BELDEN** BRAND**Product information****Compact OpenRail Fast Ethernet Switch 4-25 ports - RS20-2400T1T1SDAPH07.0.**

Industrial Ethernet:Compact configurable managed switches:with Firmware Release 7:Compact OpenRail Fast Ethernet Switch 4-25 ports

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49854-173491-173293/en/RS20-2400T1T1SDAPH07.0.uistate>

Name	Compact OpenRail Fast Ethernet Switch 4-25 ports
	
	24 port Fast-Ethernet-Switch, managed, software Layer 2 Professional, for DIN rail store-and-forward-switching, fanless design
<b>Delivery informations</b>	
Availability	available
<b>Product description</b>	
Description	24 port Fast-Ethernet-Switch, managed, software Layer 2 Professional, for DIN rail store-and-forward-switching, fanless design
Port type and quantity	24 ports in total; 1. uplink: 10/100BASE-TX, RJ45; 2. uplink: 10/100BASE-TX, RJ45; 22 x standard 10/100 BASE TX, RJ45
Type	RS20-2400T1T1SDAPH07.0.
Order No.	943 434-042
<b>More Interfaces</b>	
Power supply/signaling contact	1 x plug-in terminal block, 6-pin
V.24 interface	1 x RJ11 socket
USB interface	1 x USB to connect the AutoConfiguration Adapter ACA21-USB
<b>Network size - length of cable</b>	
Twisted pair (TP)	0 m ... 100 m
<b>Network size - cascability</b>	
Line - / star topology	any
Ring structure (HIPER-Ring) quantity switches	50 (reconfiguration time < 0.3 sec.)
<b>Power requirements</b>	
Operating voltage	12/24/48 V DC (9.6-60) V and 24 V AC (18-30) V (redundant)
Current consumption at 24 V DC	563 mA
Current consumption at 48 V DC	282 mA
Power output in Btu (IT) h	46.1
<b>Software</b>	
Management	Serial interface, web-interface, SNMP V1/V2, HiVision file transfer SW HTTP/TFTP, LLDP-MED, Voice VLAN
Diagnostics	LEDs, log-file, syslog, relay contact, RMON, port mirroring 1:1 and n:1, topology discovery 802.1AB, cable tester (TX), address conflict detection, network error detection, SFP diagnostic (temperature, optical input and output power, power in dBm), Trap for configuration saving and changing, duplex mismatch detection, disable learning, Port Monitor
Configuration	Command line interface (CLI), TELNET, BootP, DHCP, DHCP option 82, HiDiscovery, easy device exchange with auto-configuration adapter ACA21-USB (automatic software and/or configuration upload), automatic script load from ACA21, integrated DHCP server per port, automatic invalid configuration undo, Offline Configuration, SFP Whitelist, ARC automatic ring configuration (MRP), automatic port shutdown (link flapping)
Security	Port Security (IP und MAC) with multiple addresses(50 MACs per port), SNMP V3, SSH, Authentication (IEEE802.1x), 802.1x Multi Client Authentication, Guest VLAN and Unauthenticated VLAN, Port based Radius VLAN assignment
Redundancy functions	HIPER-Ring, MRP, MSTP, RSTP - IEEE802.1D-2004, MRP and RSTP in parallel, link aggregation
Filter	QoS 4 classes, prioritisation (IEEE 802.1D/p), VLAN (IEEE 802.1Q), Voice VLAN, shared VLAN learning, Q-in-Q double VLAN tagging, multicast IGMP v1/v2/v3 (snooping/querier), multicast detection unknown multicast, broadcast-, unicast-, multicast limiter, fast aging, GMRP IEEE 802.1D
Industrial Profiles	EtherNet/IP and PROFINET (2.2 PDEV, GSDML stand-alone generator, automatic device exchange) profiles included, configuration and diagnostic via automation software tools like e.g. STEP7, or Control Logix
Time synchronisation	SNTP client/server, PTP / IEEE 1588, realtime watch with energy buffer
Flow control	Flow control 802.3x, port priority 802.1D/p, priority (TOS/DIFFSERV), prio (MAC/IP), prio mapping (TOS Layer2), traffic shaping (unicast, multicast, broadcast) ingress / egress
Presettings	Standard
<b>Ambient conditions</b>	
Operating temperature	0 °C ... 60 °C
Storage/transport temperature	-40 °C ... 70 °C

**HIRSCHMANN**A **BELDEN** BRAND**Industrial Ethernet:Compact configurable managed switches:with Firmware Release 7:Compact OpenRail Fast Ethernet Switch 4-25 ports**<http://www.e-catalog.beldensolutions.com/link/57078-24455-49854-173491-173293/en/RS20-2400T1T1SDAPHH07.0/uistate>

<b>Relative humidity (non-condensing)</b>	10 % ... 95 %
<b>MTBF</b>	35.1 years (MIL-HDBK-217F)
<b>Protective paint on PCB</b>	No
<b>Mechanical construction</b>	
<b>Dimensions (W x H x D)</b>	110 mm x 131 mm x 111 mm
<b>Mounting</b>	DIN Rail
<b>Weight</b>	650 g
<b>Protection class</b>	IP20
<b>Mechanical stability</b>	
<b>IEC 60068-2-27 shock</b>	15 g, 11 ms duration, 18 shocks
<b>IEC 60068-2-6 vibration</b>	1 mm, 2 Hz-13.2 Hz, 90 min.; 0.7 g, 13.2 Hz-100 Hz, 90 min.; 3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1 g, 9 Hz-150 Hz, 10 cycles, 1 octave/min
<b>EMC interference immunity</b>	
<b>EN 61000-4-2 electrostatic discharge (ESD)</b>	6 kV contact discharge, 8 kV air discharge
<b>EN 61000-4-3 electromagnetic field</b>	10 V/m (80-1000 MHz)
<b>EN 61000-4-4 fast transients (burst)</b>	2 kV power line, 1 kV data line
<b>EN 61000-4-5 surge voltage</b>	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line
<b>EN 61000-4-6 conducted immunity</b>	3 V (10 kHz-150 kHz), 10 V (150 kHz-80 MHz)
<b>EMC emitted immunity</b>	
<b>FCC CFR47 Part 15</b>	FCC 47 CFR Part 15 Class A
<b>EN 55022</b>	EN 55022 Class A
<b>Approvals</b>	
<b>Safety of industrial control equipment</b>	cUL 508
<b>Hazardous locations</b>	cUL 1604 Class1 Div 2
<b>Shipbuilding</b>	n/a
<b>Railway norm</b>	n/a
<b>Substation</b>	n/a
<b>Scope of delivery and accessories</b>	
<b>Scope of delivery</b>	Device, terminal block, operating manual

For more information please contact:

**Hirschmann Automation and Control GmbH**

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: [inet-sales@belden.com](mailto:inet-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.

The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.