

Product information

RS2-5TX/FX (alt_old)

Industrial Ethernet:Archive - Industrial Ethernet:Entry Level Hubs And Switches:Unmanaged Rail-Switches:RS2-5TX/FX (alt_old)

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49814-49855-24475-40990/en/conf/ui/state>

Name	RS2-5TX/FX (alt_old)
	
	Unmanaged Industrial ETHERNET Rail-Switch, store and forward switching mode, Ethernet (10 Mbit/s) and Fast-Ethernet (100 Mbit/s)
Delivery informations	
Availability	no longer available
Product description	
Description	Unmanaged Industrial ETHERNET Rail-Switch, store and forward switching mode, Ethernet (10 Mbit/s) and Fast-Ethernet (100 Mbit/s)
Port type and quantity	4 x 10/100BASE-TX, TP cable, RJ45 sockets, auto-crossing, auto-negotiation, auto-polarity, 1 x 100BASE-FX, MM cable, MTRJ socket
Type	RS2-5TX/FX (alt_old)
Order No.	943 732-102
replaced by	RS2-5TX/FX
More Interfaces	
Power supply/signaling contact	1 plug-in terminal block, 5-pin / no signal contact
Network size - length of cable	
Twisted pair (TP)	0 - 100 m
Multimode fiber (MM) 50/125 µm	0 - 5000 m, 8 dB link budget at 1300 nm, A = 1 dB/km, 3 dB reserve, B = 800 MHz x km
Multimode fiber (MM) 62.5/125 µm	0 - 4000 m, 11 dB link budget at 1300 nm, A = 1 dB/km, 3 dB reserve, B = 500 MHz x km
Network size - cascadiability	
Line - / star topology	any
Power requirements	
Operating voltage	24 V DC (-25% to +30%)
Current consumption at 24 V DC	max. 180 mA
Power consumption	max. 4,0 W at 24 V DC
Service	
Diagnostics	LEDs (power, link status, data, error)
Redundancy	
Redundancy functions	redundant 24 V power supply
Ambient conditions	
Operating temperature	0 °C to +60 °C
Storage/transport temperature	-25 °C to +70 °C
Relative humidity (non-condensing)	10% to 95%
MTBF	74,4 years; MIL-HDBK 217F: Gb 25 °C
Mechanical construction	
Dimensions (W x H x D)	40 mm x 145 mm x 80 mm
Mounting	DIN Rail 35 mm
Weight	520 g
Protection class	IP 20
Mechanical stability	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	3.5 mm, 3 Hz - 9 Hz, 10 cycles, 1 octave/min.; 1g, 9 Hz - 150 Hz, 10 cycles, 1 octave/min.
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m
EN 61000-4-4 fast transients (burst)	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage	power line: 1 kV (line/earth), 0.5 kV (line/line), 1 kV data line
EN 61000-4-6 conducted immunity	10 V (150 kHz - 80 MHz)

Industrial Ethernet:Archive - Industrial Ethernet:Entry Level Hubs And Switches:Unmanaged Rail-Switches:RS2-5TX/FX (alt_old)
<http://www.e-catalog.beldensolutions.com/link/57078-24455-49814-49855-24475-40990/en/conf/ui.state>
EMC emitted immunity
FCC CFR47 Part 15 FCC CFR47 Part 15 Class A

EN 55022 EN 55022 Class A

Approvals
Safety of industrial control equipment cUL 508 (E175531)

Safety of information technology equipment cUL 60950 (E168643)

Scope of delivery and accessories
Scope of delivery device, terminal block, operating manual

Accessories to order separately rail power supply RPS 30, RPS 80 EEC or RPS 120 EEC, 19" installation frame

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

 E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.