

Product information

EAGLE 20 TX/SM

Industrial Ethernet:Industrial Firewall System:EAGLE 20 Industrial Firewall / VPN-Router:EAGLE 20 TX/SM

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49853-24495-40972/en/conf/ui/state>

Name	EAGLE 20 TX/SM
	
	Industrial Firewall/VPN-Router
Delivery informations	
Availability	available
Product description	
Description	Industrial Firewall/VPN-Router
Modi	Router, Transparent (Bridging), Multipoint VPN (Router, PPPoE)
Port type and quantity	Trusted port: 1 x 10/100BASE-TX, TP-cable, RJ45-socket, autocrossing, autonegotiation, autopolarity Untrusted port: 1 x 100BASE-FX, SM-cable, SC-socket
Type	EAGLE 20 TX/SM
Order No.	943 987-003
More Interfaces	
Power supply/signaling contact	1 x plug-in terminal block, 6-pin
V.24 interface	1 x RJ11 socket (serial interface for device configuration)
USB interface	1 x USB socket (to connect auto-configuration adapter ACA21-USB)
Network size - length of cable	
Twisted pair (TP)	0 - 100 m
Multimode fiber (MM) 50/125 µm	n/a
Multimode fiber (MM) 62.5/125 µm	n/a
Single mode fiber (SM) 9/125 µm	0 - 32.5 km, 16 dB link budget at 1300 nm, A = 0.4 dB/km, 3 dB Reserve, D = 3.5 ps/(nm x km)
Security	
Stateful inspection firewall	firewall rules (incoming/outgoing, modem access, management), IP masquerading, 1-to-1 NAT, DoS limiter, MAC filter, user firewall for external activation of FW rules
Multipoint VPN	IPSec, IKEv2, DES, 3DES, AES (-128, -192, -256), Pre-Shared Key, X.509v3 certificates, MD5, SHA-1, NAT-T, Firewall rules for every VPN connection, configuration assistant in the Web-interface, remote enable/disable of connections.
Power requirements	
Operating voltage	DC 9.6 to 60 V, AC 18 to 30 V
Current consumption at 24 V DC	max. 8.1 W
Service	
Management	Command Line Interface (CLI), Web-Interface, Auto-configuration adapter (ACA21-USB), DHCP, HiDiscovery, Industrial HiVision
Diagnostics	LEDs (power, link status, data, error, ACA, V.24), signal contact (DC 24 V / 1 A), logfile, syslog, configuration check
Protocols	serial, HTTPS, SSH, SNMP V1/V2/V3, LLDP
Other services	DHCP server/client, DHCP Relay/Option 82, DynDNS, firewall access via V.24 (PPP), SNTP, VLAN support (IEEE 802.3pQ), port forwarding
Redundancy	
Redundancy functions	use in redundant network/ring coupling, firewall redundancy (Layer 4), redundnat 24 V power inputs
Ambient conditions	
Operating temperature	0 °C to +60 °C
Storage/transport temperature	-40 °C to +70 °C
Relative humidity (non-condensing)	10% to 95%
MTBF	25.2 years; MIL-HDBK 217F: Gb 25 °C
Mechanical construction	
Dimensions (W x H x D)	60 mm x 145 mm x 125 mm
Mounting	DIN Rail 35 mm
Weight	615 g



Industrial Ethernet:Industrial Firewall System:EAGLE 20 Industrial Firewall / VPN-Router:EAGLE 20 TX/SM

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49853-24495-40972/en/conf/ui/state>

Protection class	IP 20
Mechanical stability	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	1 mm, 2 Hz - 13.2 Hz, 90 min.; 0.7g, 13.2 Hz - 100 Hz, 90 min.; 3.5 mm, 3 Hz - 9 Hz, 10 cycles, 1 octave/min.; 1g, 9 Hz - 150 Hz, 10 cycles, 1 octave/min
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	6 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80 - 2000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (linie/earth), 1 kV (linie/line)
EN 61000-4-6 conducted immunity	3 V (10 kHz - 150 kHz), 10 V (150 kHz - 80 MHz)
EMC emitted immunity	
FCC CFR47 Part 15	FCC CFR47 Part 15 Class A
EN 55022	EN 55022 Class A
Approvals	
Safety of industrial control equipment	cUL 508
Germanischer Lloyd	Germanischer Lloyd
Scope of delivery and accessories	
Scope of delivery	device, terminal block, operating instructions, CD-manual
Accessories to order separately	rail power supply RPS 30, RPS 80 EEC, RPS 120 EEC, terminal cable, network management Industrial HiVision, modem cable, auto-configuration adapter ACA21-USB, 19" installation frame

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.

The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.