


640 Series CMP Cat 6A UTP Cable

TE640P



Description

TE Connectivity's 640 Series UTP cable enables 10 Gigabit Ethernet performance with an industry-low outside diameter. The 640 Series Category 6A plenum cables feature the best in class AirES® technology. This patented design saves as much as 32% of the available space in cable runs and is a key component of the TE structured cabling system. The smaller diameter also saves space in the communications closet, reduces the amount of cable management accessories required and lowers the risk associated with fire and smoke in the plenum space. TE's 640 cable also features a patented oblique elliptical offset filler to minimize alien crosstalk.

TE Connectivity Category 6A cables exceed ANSI/TIA-568-C Category 6A and ISO/IEC 11801 Category 6A performance requirements by significant margins on all parameters. The TE Connectivity Category 6A System complies with all of the performance requirements for current and proposed applications such as Gigabit Ethernet (1000BASE-Tx), 10/100BASE-Tx, token ring, 155 Mbps ATM, 100 Mbps TP-PMD, ISDN, analog and digital video and analog and digital voice (VoIP).

TE Connectivity Category 6A UTP cables are available in standard colors including white, gray, blue and yellow. Category 6A Cables from TE feature lead-free jacketing. Packaging is on reels with standard put-ups being 1000 ft splice-free lengths.

Specification

Horizontal cabling shall be 23 AWG, 4-pair UTP, NEC/NFPA CMP rated and be independently verified for compliance. Cable jacketing shall be white, gray, blue or yellow and shall be lead-free. Individual conductors shall be 100% virgin FEP insulated. Cable shall exceed all ANSI/TIA and ISO Category 6A requirements as well as meet the performance requirements listed in the table shown on page 2.

Cable performance shall be verified and characterized to 650 MHz. Cable shall be supplied on reels. Independent verification for flammability compliance shall be to NEC article 800 and NFPA 70; NFPA 262. Horizontal cable shall be TE catalog number TE640P-XXYY.

640 Series CMP Cat 6A UTP Cable

TE640P

PERFORMANCE DATA

FREQ MHZ	FITTED IMPEDANCE Ohms	INSERTION LOSS dB/100 m		RETURN LOSS dB/100 m		PAIR-PAIR NEXT dB/100 m		PSNEXT dB/100 m	
	Spec	Max	Spec	Min	Spec	Min	Spec	Min	Spec
1	100 +/- 5	1.8	2.1	29.1	20.0	87.9	75.3	86.7	72.3
4	100 +/- 3	3.5	3.8	31.1	23.0	75.5	66.3	74.4	63.3
8	100 +/- 3	4.9	5.3	36.0	24.5	68.9	61.8	66.9	58.8
10	100 +/- 3	5.6	5.9	36.9	25.0	69.1	60.3	66.4	57.3
16	100 +/- 3	7.1	7.5	33.6	25.0	66.7	57.2	66.2	54.2
20	100 +/- 3	7.9	8.4	38.7	25.0	66.4	55.8	63.8	52.8
25	100 +/- 3	8.9	9.4	41.4	24.3	64.0	54.3	61.2	51.3
31.25	100 +/- 3	10.0	10.5	37.9	23.6	63.1	52.9	60.8	49.9
62.5	100 +/- 3	14.2	15.0	34.2	21.5	65.8	48.4	63.8	45.4
100	100 +/- 3	18.0	19.1	35.8	20.1	53.7	45.3	51.5	42.3
155	100 +/- 3	22.7	24.1	31.6	18.8	54.1	42.4	51.5	39.4
200	100 +/- 3	25.9	27.6	30.2	18.0	49.8	40.8	46.9	37.8
250	100 +/- 3	29.0	31.1	29.2	17.3	46.7	39.3	45.8	36.3
300	100 +/- 3	31.8	34.3	30.2	17.3	53.2	38.1	50.0	35.1
350	100 +/- 3	34.4	37.2	27.6	17.3	42.2	37.1	40.7	34.1
400	100 +/- 3	37.0	40.1	26.0	17.3	41.5	36.3	40.1	33.3
450	100 +/- 3	39.5	42.7	27.9	17.3	37.9	35.5	37.3	32.5
500	100 +/- 3	41.6	45.3	26.2	17.3	43.7	34.8	39.2	31.8
550	100 +/- 3	43.8	-	23.2	-	42.8	-	40.0	-
600	100 +/- 3	45.7	-	24.2	-	44.8	-	42.7	-
650	100 +/- 3	47.8	-	21.5	-	34.2	-	32.4	-

PERFORMANCE DATA

FREQ MHZ	PAIR-PAIR ACR dB/100 m		PSACR dB/100 m		PAIR-PAIR ACRF dB/100 m		PSACRF dB/100 m		TCL dB/100 m	ELTCTL dB/100 m
	Min	Spec	Min	Spec	Min	Spec	Min	Spec	Min	Min
1	86.2	73.2	84.9	70.2	79.5	68.0	76.3	65.0	40.0	35.0
4	72.0	62.5	71.0	59.5	67.6	56.0	64.4	53.0	40.0	23.0
8	64.0	56.4	62.0	53.4	62.0	49.9	58.5	46.9	40.0	16.9
10	63.6	54.4	60.9	51.4	59.9	48.0	56.5	45.0	40.0	15.0
16	59.8	49.8	59.1	46.8	56.4	43.9	52.7	40.9	38.0	10.9
20	58.6	47.4	56.0	44.4	54.6	42.0	50.7	39.0	37.0	9.0
25	55.3	45.0	52.5	42.0	52.6	40.0	48.8	37.0	36.0	7.0
31.25	53.3	42.4	51.1	39.4	51.0	38.1	47.0	35.1	35.1	-
62.5	51.8	33.4	49.9	30.4	44.6	32.1	41.4	29.1	32.0	-
100	35.9	26.2	33.5	23.2	40.0	28.0	37.6	25.0	30.0	-
155	31.9	18.4	28.8	15.4	35.6	24.2	32.6	21.2	28.1	-
200	24.5	13.2	21.0	10.2	33.6	22.0	32.3	19.0	27.0	-
250	18.4	8.3	17.4	5.3	31.9	20.0	28.0	17.0	26.0	-
300	22.0	3.9	18.9	0.9	30.0	18.5	26.6	15.5	25.2	-
350	8.5	-0.1	6.3	-3.1	27.7	17.1	24.3	14.1	24.6	-
400	5.3	-3.8	3.1	-6.8	25.2	16.0	22.2	13.0	24.0	-
450	-0.6	-7.2	-1.8	-10.2	23.3	14.9	22.1	11.9	23.5	-
500	3.0	-10.4	-1.4	-13.4	22.4	14.0	21.3	11.0	23.0	-
550	0.0	-	-2.8	-	22.5	-	21.4	-	-	-
600	-0.1	-	-2.2	-	23.8	-	20.4	-	-	-
650	-12.5	-	-14.4	-	25.3	-	19.2	-	-	-

NOTE: The above listed discrete frequency electrical performance values are provided for engineering information only. Actual compliance testing is based on swept frequency measurements.

640 Series CMP Cat 6A UTP Cable

TE640P

SPECIFICATIONS

Mutual Capacitance:	5.6 nF/100 m maximum
Conductor DC Resistance:	28.6 Ω /1000 ft (9.38 Ω /100 m) maximum
Voltage:	300 VDC
Delay Skew:	40 ns/100 m
Propagation Delay:	480 ns/100 m @ 250 MHz
Nominal Velocity of Propagation:	69%
Operating Temperature:	-20° C - 60° C (-4° F - 140° F)
Storage Temperature:	-20° C - 80° C (-4° F - 176° F)
Installation Temperature:	5° C - 50° C (41°F - 122°F)
Bend Radius:	4 × cable diameter
Packaging:	1000' Reel-in-a-box: 43 lbs/kft 1000' Reel: 41 lbs/kft
Materials:	Conductors: 23 AWG, Solid Copper (0.0230" nominal) Insulation: 0.043 nominal, FEP Jacket: 0.285" nominal, FR PVC
Compliances:	UL Subject 444 (UL)-C(UL) Type CMP ICEA S-90-661 ETL Verified TIA-568-C.2 Category 6A Horizontal Cable Requirements ISO/IEC 11801 Category 6A Horizontal Cable Requirements 2002/95/EC RoHS



ORDERING INFORMATION

Product Description	Packaging	Part Number
Category 6A UTP Cable,4-Pair, Plenum (CMP) Rated	1000' Reel	TE640P-XX02

*Additional reel sizes available, please contact TE customer service.

The following jacket colors are available. Replace XX with:

BL= Blue	WT=White	GY=Gray	YL=Yellow	GN=Green
BK=Black	RD=Red	OR=Orange	VT=Violet	BN=Brown

DATA SHEET



Contact us:
Greensboro, NC
USA 27409-8420
Tel: 1-800-553-0938
Fax: 1-717-986-7406

www.te.com/EnterpriseNetworks

TE Connectivity, TE connectivity (logo), Tyco Electronics, TE (logo), AirES are trademarks of the TE Connectivity Ltd. family of companies and its licensors.

While TE Connectivity has made every reasonable effort to ensure the accuracy of the information in this document, TE Connectivity does not guarantee that it is error-free, nor does TE Connectivity make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE Connectivity reserves the right to make any adjustments to the information contained herein at any time without notice. TE Connectivity expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE Connectivity for the latest dimensions and design specifications.

Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.

312662AE 10/12 Revision © 2012