



Product information MM3-4FXP4

Industrial Ethernet:Archive - Industrial Ethernet:Modular Industrial Switches:Modular switches:Ethernet / Fast-Ethernet POF media modules:MM3-4FXP4

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49814-49860-49862-24488-37862/en/conf/uistate>

Name	MM3-4FXP4
	
	Media module for MICE Switches (MS...), 100BASE-FX multi-mode F/O, POF and HCS
Delivery informations	
Availability	no longer available
Product description	
Description	Media module for MICE Switches (MS...), 100BASE-FX multi-mode F/O, POF and HCS
Port type and quantity	4 x 100BASE-FX, MM cables, ST sockets
Type	MM3-4FXP4
Order No.	943 843-101
replaced by	Fast Ethernet MICE Media Modules, standard - MM20-T1T1T1T1SAHH
Network size - length of cable	
Multimode fiber HCS (MM) 200/230 µm	0 - 140 m 9 dB link budget at 650 nm A = 10 dB/km, 3 dB reserve, B = 17 MHz x km
Multimode fiber POF (MM) 980/1000 µm	0 - 65 m 14 dB link budget at 650 nm A = 160 dB/km, 3 dB reserve, B = >10 MHz x km, low-NA-POF
Power requirements	
Operating voltage	power supply via the backplane of the MICE switch
Power consumption	3,4 W
Service	
Diagnostics	LEDs (power, link status, data, 100 Mbit/s, full duplex, ring port, LED test)
Ambient conditions	
Operating temperature	0 °C bis +60 °C standart (optional -40°C to +70°C)
Storage/transport temperature	-40 °C to +70 °C
Relative humidity (non-condensing)	10% to 95%
MTBF	48,8 Jahre; MIL-HDBK 217F: Gb 25 °C
Mechanical construction	
Dimensions (W x H x D)	38 mm x 134 mm x 77 mm
Mounting	Backplane
Weight	324 g
Protection class	IP 20
Mechanical stability	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	1 mm, 2 Hz - 13.2 Hz, 90 min.; 0.7g, 13.2 Hz - 100 Hz, 90 min.; 3.5 mm, 3 Hz - 9 Hz, 10 cycles, 1 octave/min.; 1g, 9 Hz - 150 Hz, 10 cycles, 1 octave/min.
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80 - 1000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line,
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line),
EN 61000-4-6 conducted immunity	3 V (10 kHz - 150 kHz), 10 V (150 kHz - 80 MHz)
EMC emitted immunity	
FCC CFR47 Part 15	FCC CFR47 Part 15 Class A
EN 55022	EN 55022 Class A



Industrial Ethernet:Archive - Industrial Ethernet:Modular Industrial Switches:Modular switches:Ethernet / Fast-Ethernet POF media modules:MM3-4FXP4

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49814-49860-49862-24488-37862/en/conf/ulistate>

Approvals

Safety of industrial control equipment	cUL 508
Hazardous locations	cUL 1604 Class1 Div 2 (pending)
Shipbuilding	Germanischer Lloyd
Substation	optional
Railway norm	optional

Scope of delivery and accessories

Scope of delivery	module, operating manual
Accessories to order separately	ML-MS2/MM labels

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.