

156-00589

Cable Tie and Edge Clip, 50lb, 7.9", EC5A Pan Thickness .04"-.12", PA66UV Tie, HIRHS MNT, 100/pk

Article Number: 156-00589

Part Number: 156-00589

Type: T50REC5A



1. Base Data

Part No.	156-00589
Type	T50REC5A
Color	Black (BK)
Features	HellermannTyton's UV stabilized tie and edge clip assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.
Application	The UV stabilized tie and edge clip assemblies are ideal for use where holes are not available or where adhesives are not strong enough. Edge clips are widely used for fixing and bundling cables and wires in the automotive, harness making, panel building and renewable energy industry.
Variant	Inside Serrated

2. Product Dimensions

Min. Tensile Strength	50 lbs / 225 N
Length (L)	8.0 " / 200.0 mm
Length (L2)	.0551 " / 14.0 mm
Width (W)	4.6 mm
Width (W2)	0.394 " / 10.0 mm
Height (H)	.0472 " / 1.2 mm

Min. Ø Bundle	.16 " / 4.0 mm
Max. Ø Bundle	1.8 " / 45.0 mm
Max. Panel Thickness	0.12 " / 3.0 mm
Min. Panel Thickness	0.04 " / 1.0 mm
Thickness	1.2 mm

4. Material and Specifications

Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS) / Polyamide 6.6 UV-stabilized (PA66UV)
Material Shortcut	PA66HIRHS / PA66UV
Cable Tie	Polyamide 6, UV stabilised (PA6UV)
Edge Clip	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS) / Stainless Steel (SS)
Operating Temperature	-40 °F to +221 °F (-40 °C to +105 °C)
Operating Temperature Foot Part (Metric)	-40 °F to +221 °F (-40 °C to +105 °C)
ROHS Conformity	 RoHS

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	100