

PTFE

250° C 300/600Volts

Ratings/Approvals

300 Volts - UL Style 1815 / CSA AWM I A/B FT1

600 Volts - UL Style 1659 / CSA AWM I A/B FT1

Construction

Stranded nickel plated copper conductor

Extruded Polytetrafluoroethylene (PTFE)

Standard color coding available

300 Volt		
AWG (Stranding)	OD	Weight/mft
24(19)	.050"	3
22(19)	.056"	4
20(19)	.061"	6
18(19)	.070"	8
16(19)	.082"	11
14(19)	.095"	17
12(19)	.115"	25
10(37)	.147"	40

600 Volt		
AWG (Stranding)	OD	Weight/mft
24(19)	.064"	5
22(19)	.070"	6
20(19)	.075"	7
18(19)	.084"	10
16(19)	.096"	13
14(19)	.109"	19
12(19)	.129"	28
10(37)	.157"	43

Consult factory for alternate conductor and stranding options.