

**HIRSCHMANN**A **BELDEN** BRAND**Product information****Modular OpenRail Fast Ethernet switch 8-24 ports -  
MS20-0800SAAEHH07.0.****Industrial Ethernet:Modular Industrial Switches:Configurable modular switches:with Firmware Release 7:Modular OpenRail Fast Ethernet switch 8-24 ports**<http://www.e-catalog.beldensolutions.com/link/57078-24455-49860-49861-168503-168504/en/MS20-0800SAAEHH07.0/uistate>

Name	Modular OpenRail Fast Ethernet switch 8-24 ports
	8 port Fast Ethernet switch, managed, software Layer 2 Enhanced, for DIN rail store-and-forward-switching, fanless design
<b>Delivery informations</b>	
Availability	available
<b>Product description</b>	
Description	8 port Fast Ethernet switch, managed, software Layer 2 Enhanced, for DIN rail store-and-forward-switching, fanless design
<b>Port type and quantity</b>	Fast Ethernet ports in total: 8; Gigabit Ethernet ports: 0
Type	MS20-0800SAAEHH07.0.
Order No.	943 435-001
<b>More Interfaces</b>	
Power supply/signaling contact	2 x plug-in terminal block, 4-pin
V.24 interface	1 x RJ11 socket
USB interface	1 x USB to connect the AutoConfiguration Adapter ACA21-USB
<b>Network size - cascability</b>	
Line / star topology	any
Ring structure (HIPER-Ring) quantity switches	50 (reconfiguration time < 0.3 sec.)
<b>Power requirements</b>	
Operating voltage	24 V DC (18-32) V
Current consumption at 24 V DC	208 mA
Current consumption at 48 V DC	155 mA
Power output in Btu (IT) h	17.1
<b>Software</b>	
Management	Serial interface, web interface, SNMP V1/V2, Hivision file transfer SW HTTP/TFTP
Diagnostics	LEDs, log-file, syslog, relay contact, RMON, port mirroring 1:1, topology discovery 802.1AB, disable learning, SFP diagnostic (temperature, optical input and output power, power in dBm)
Configuration	Command line interface (CLI), TELNET, BootP, DHCP, DHCP option 82, HIDiscovery, easy device exchange with auto-configuration adapter ACA21-USB (automatic software and/or configuration upload), automatic invalid configuration undo,
Security	Port Security (IP und MAC) with multiple addresses(50 MACs per port), SNMP V3 (without encryption)
Redundancy functions	HIPER-ring (ring structure), MRP (IEC-ring functionality), RSTP 802.1D-2004, redundant network/ring coupling, MRP and RSTP in parallel, redundant 24 V power supply
Filter	QoS 4 classes, port prioritisation (IEEE 802.1D/p), VLAN (IEEE 802.1Q), shared VLAN learning, multicast (IGMP Snooping/Querier), multicast detection unknown multicast, broadcastlimiter, fast aging
Industrial Profiles	EtherNet/IP and PROFINET (2.2 PDEV, GSDML stand-alone generator, automatic device exchange) profiles included, configuration and diagnostic via automation software tools like e.g. STEP7, or Control Logix
Time synchronisation	SNTP server, PTP / IEEE 1588
Flow control	Flow control 802.3x, port priority 802.1D/p, priority (TOS/DIFFSERV)
Presettings	Standard
<b>Ambient conditions</b>	
Operating temperature	0 °C ... 60 °C
Storage/transport temperature	-40 °C ... 70 °C
Relative humidity (non-condensing)	10 % ... 95 %
MTBF	54.7 years (MIL-HDBK-217F)
Protective paint on PCB	No

**HIRSCHMANN**A **BELDEN** BRAND**Industrial Ethernet:Modular Industrial Switches:Configurable modular switches:with Firmware Release 7:Modular OpenRail Fast Ethernet switch 8-24 ports**<http://www.e-catalog.beldensolutions.com/link/57078-24455-49860-49861-168503-168504/en/MS20-0800SAEHH07.0./uistate>**Mechanical construction**

<b>Dimensions (W x H x D)</b>	125 mm x 133 mm x 100 mm (140 at 48V module)
<b>Mounting</b>	DIN Rail
<b>Weight</b>	610 g
<b>Protection class</b>	IP20

**Mechanical stability**

<b>IEC 60068-2-27 shock</b>	15 g, 11 ms duration, 18 shocks
<b>IEC 60068-2-6 vibration</b>	1 mm, 2 Hz-13.2 Hz, 90 min.; 0.7 g, 13.2 Hz-100 Hz, 90 min.; 3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1 g, 9 Hz-150 Hz, 10 cycles, 1 octave/min

**EMC interference immunity**

<b>EN 61000-4-2 electrostatic discharge (ESD)</b>	6 kV contact discharge, 8 kV air discharge
<b>EN 61000-4-3 electromagnetic field</b>	10 V/m (80-1000 MHz)
<b>EN 61000-4-4 fast transients (burst)</b>	2 kV power line, 1 kV data line
<b>EN 61000-4-5 surge voltage</b>	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line
<b>EN 61000-4-6 conducted immunity</b>	3 V (10 kHz-150 kHz), 10 V (150 kHz-80 MHz)

**EMC emitted immunity**

<b>FCC CFR47 Part 15</b>	FCC 47 CFR Part 15 Class A
<b>EN 55022</b>	EN 55022 Class A

**Approvals**

<b>Safety of industrial control equipment</b>	cUL 508
<b>Hazardous locations</b>	cUL 1604 Class1 Div 2
<b>Shipbuilding</b>	n/a
<b>Railway norm</b>	n/a
<b>Substation</b>	n/a
<b>Transportation</b>	NEMA TS2

**Scope of delivery and accessories**

<b>Scope of delivery</b>	Device, 2 x terminal block, operating manual, CD
--------------------------	--

For more information please contact:

**Hirschmann Automation and Control GmbH**  
Stuttgarter Strasse 45-51  
72654 Neckartenzlingen  
Germany  
Phone: +49 7127/14-1809  
E-Mail: [inet-sales@belden.com](mailto:inet-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.  
The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.