Detailed Specifications & Technical Data




For more Information please call

ENGLISH MEASUREMENT VERSION

1382LP Multi-Conductor - Commercial AV, Automation/Lighting Control Cable





Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

1382LP Multi-Conductor - Commercial AV, Automation/Lighting Control Cable

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	05/07/12
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Flame Test	
UL Flame Test:	UL910 Plenum
CSA Flame Test:	FT6
Plenum/Non-Plenum	
Plenum (Y/N):	Yes
Non-Plenum Number:	1382LA, 1383LA

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft) 13.000

Nom. Conductor DC Resistance:

DCR @ 20°C	(Ohm/1000 f
4.200	

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Current 9.1 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1382LP 3681000	1,000 FT	26.000 LB	CLEAR, TRANSPARENT		2 #16 FEP FEP

Revision Number: 1 Revision Date: 02-15-2013

© 2013 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this products are subject to beiden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the action before the product for the one that it become a part of This Product Disclosure is not for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.