


1386LP Multi-Conductor - Lighting Control Cable

For more Information
please call

1-800-Belden1



General Description:

1 - pr. 22 AWG stranded (7x30) bare copper conductors, plenum, FEP insulation (data), STP w/Beldfoil®; 1 - 18 AWG (19x30) bare copper conductor unshielded, FEP insulation (power); 2 - 12 AWG (19x25) bare copper conductors, unshielded, FEP insulation, Flamarrest® jacket.

Usage (Overall)

Suitable Applications: Automation/Lighting Control

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	# Pairs	AWG	Stranding	Conductor Material
	1	22	7x30	BC - Bare Copper
1		18	19x30	BC - Bare Copper
2		12	19x25	BC - Bare Copper

Total Number of Conductors: 5

Insulation

Insulation Material:

Insulation Material	AWG
FEP - Fluorinated Ethylene Propylene	22
FEP - Fluorinated Ethylene Propylene	18
FEP - Fluorinated Ethylene Propylene	12

Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)	Stranding	Dia. (in.)	Conductor Material
22 AWG Pair	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100			

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride

Outer Jacket Ripcord: No

Overall Cable

Overall Nominal Diameter: 0.300 in.

Pair

Pair Color Code Chart:

Number	Color
1	Purple & White (22awg)
2	Red & Black (12awg)
3	Org (18awg)

Mechanical Characteristics (Overall)

Operating Temperature Range:	0°C To +60°C
Bulk Cable Weight:	86 lbs/1000 ft.
Max. Recommended Pulling Tension:	194 lbs.
Min. Bend Radius/Minor Axis:	3 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CL3P, CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262 Plenum Flame Test (UL910)(FT6)
CSA Flame Test:	FT6

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	1386LA

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Description	Capacitance (pF/ft)
22 AWG Pair	21.200

Nom. Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/1000 ft)
22AWG	16.100
18AWG	6.500
12AWG	1.600

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Description	Current
22AWG	3.8 Amps per conductor @ 25°C

1386LP Multi-Conductor - Lighting Control Cable

18AWG	7.2 Amps per conductor @ 25°C
12AWG	17.2 Amps per conductor @ 25°C

Notes (Overall)

Notes: Sequential footage marking every two feet.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1386LP 0091000	1,000 FT	90.000 LB	WHITE		1FSPR #22+2 #12+1#18 FEP FLRST
1386LP 009250	250 FT	24.500 LB	WHITE		1FSPR #22+2 #12+1#18 FEP FLRST
1386LP 009500	500 FT	46.500 LB	WHITE		1FSPR #22+2 #12+1#18 FEP FLRST

Revision Number: 1 Revision Date: 08-30-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.