



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SRWO8U22

8U, 12U or 22U Wall-Mount Open Frame Rack



Highlights

- Assemble as 8U, 12U or 22U (all required parts included)
- Open frame with 2 post mounting, 19" wide, 18" Depth
- Threaded (12-24) mounting holes
- Heavy duty steel frame
- Easy assembly

Description

Designed with provisions to integrate wall mounting, easy equipment access and cable management, SmartRack wall-mounted open frame cabinets are perfect for network equipment in IT environments with limited floor space. The 19" wide open frame rack is a heavy duty open frame rack designed for secure, high density servers and networking applications in IT environments. Rack can assemble as an 8U, 12U or 22U all from same sku and all additional parts needed are included.

Package Includes

- (1) 3mm L-Shaped Hex Key
- (2) Top/Bottom Panel Frames
- (2) Short Vertical Mounting Rails
- (2) Long Vertical Mounting Rails
- (9) M5 Button Head Cap Screws
- (24) #12-24 Equipment Mounting Screws
- Expansion Kit (packaged separately)
- (1) 3mm L-shaped Hex Key
- (2) Mounting Rail Tie Plates
- (9) M5 Button Head Cap Screws
- (8) Zip Ties

Features

- Assembles as 8U, 12U or 22U all from single sku (all extra parts are included)
- 2 post wall mounting...EIA 19" width
- Threaded (12-24) mounting holes
- Heavy duty steel construction
- Durable black textured powder coat finish
- Easy Assembly

Specifications

PHYSICAL	
Installed whole system maximum rack depth (inches)	18

Installed whole system maximum rack depth (cm)	45.72
Installed whole system total rack space height (rack spaces)	8U, 12U or 22U
Shipping weight (lbs)	16
Shipping weight (kg)	7.25
Shipping Dimensions (HWD/in)	3.03 x 20.28 x 18.70
Shipping Dimensions (HWD/cm)	7.69 x 51.51 x 47.49
Unit weight (lbs)	13.77
Unit weight (kg)	6.24
Unit Dimensions (cm)	EXTERNAL DIMENSIONS: 0 x 51 x 46.32 (HWD)
Unit Dimensions (in)	EXTERNAL DIMENSIONS: 0 x 20.11 x 18.24 (HWD)
Color	Black
Weight Capacity - Stationary (lbs)	150
Weight Capacity - Stationary (kg)	68.0
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?variables.txtModelID=4745.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.