

Product information

OZD FIP G3 T

Fiber Interfaces:Fieldbus Repeater:WorldFIP LWL-Repeater:OZD FIP G3 T

<http://www.e-catalog.beldensolutions.com/link/57078-57141-57128-57132-38165/en/conf/uistate>

Name	OZD FIP G3 T
	
	interface converter electrical/optical for FIP-field bus networks; repeater function; for quartz glass und PCF (HCS) FO; integrated bus termination
Delivery informations	
Availability	available
Product description	
Description	interface converter electrical/optical for FIP-field bus networks; repeater function; for quartz glass und PCF (HCS) FO; integrated bus termination
Port type and quantity	2 x optical: 4 sockets BF0C 2.5 (STR) 1 x electrical: Sub-D 9-pin, male, pin assignment acc. to French Standard NF-C 46-604
Type	OZD FIP G3 T
Order No.	933 847-521
Electrical interface	
Signal type	World FIP
Bit rate	1 Mbit/s
Signal delay time (optional input/output)	<1 µs
Input/output signal	FIP Bus
Length of FIP cable	100 m
Connection capability	max. 16 terminal data devices
Terminator	yes, 150 Ohm
Galvanic isolation	shielding/housing: no; data lines/housing: yes
Optical interface	
Wavelength	860 nm
Cascadability	at a maximal line attenuation of the optical network with fiber G 50/125: 0 ... 60 dB with fiber G 62.5/125: 0 ... 75 dB with fiber S 200/230: 0 ... 60 dB
More Interfaces	
Power supply	5-pin terminal block, screw mounting
Signaling contact	5-pin terminal block, screw mounting
Network size - length of cable	
Multimode fiber (MM) 50/125 µm	2500 m 11 dB link budget at 860 nm; A = 3 dB/km, 3 dB reserve
Multimode fiber (MM) 62.5/125 µm	2500 m 12 dB link budget at 860 nm; A = 3.5 dB/km, 3 dB reserve
Multimode fiber HCS (MM) 200/230 µm	1500 m 16 dB link budget at 860 nm; A = 8 dB/km, 3 dB reserve
Power requirements	
Operating voltage	24 VDC -20% ... 48 VDC +10% non-interchangeable, safety extra-low voltage
Current consumption	150 mA at +24 VDC; 85 mA at + 48 VDC
Power consumption	4.1 W
Redundancy	
Redundancy functions	HIPER-Ring (ring structure), redundant 24 V infeed
Ambient conditions	
Operating temperature	0 °C to +60 °C
Storage/transport temperature	-40 °C to +70 °C
Relative humidity	<95% (non-condensing)



Fiber Interfaces:Fieldbus Repeater:WorldFIP LWL-Repeater:OZD FIP G3 T

<http://www.e-catalog.beldensolutions.com/link/57078-57141-57128-57132-38165/en/conf/ui/state>

Mechanical construction

Dimensions (W x H x D)	40 x 111 x 73.5 mm
Mounting	DIN rail or mounting plate
Weight	500 g
Protection class	IP 40
Housing material	die-cast zinc

Approvals

Issued or requested approvals	C-Tick
--------------------------------------	--------

Scope of delivery and accessories

Scope of delivery	device, start-up instructions
Accessories to order separately	manual, order no. 933 847-901

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.