



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SR42UBEXP

### 42U SmartRack Premium Enclosure (no side panels included)



#### Highlights

- 42U SmartRack enclosure with doors and NO side panels. 'EXP' version is an expansion model for when several cabinets are bayed together
- 4 interior vertical posts with unthreaded square hole openings
- Standard 24" (600mm) width and 42" (1050mm) depth for optimizing floor space
- Ships fully assembled
- Massive front to rear ventilation capacity
- 3000 lb stationary / 2250 lb rolling load capacity
- Locking, removable, reversible front and rear doors
- Rolls through standard 7 foot doorway

#### Description

The SR42UBEXP is an expansion model used when several cabinets are bayed together. It has doors and a roof but no side panels. Its integrated baying tabs make it easy to combine multiple enclosures in rows for data center application. The SR42UBEXP is also compatible with hot aisle/cold aisle configurations.

The SR42UBEXP houses 3000lbs of standard 19-inch rack equipment in 42U. Offers vendor-neutral square hole/cage nut mounting for guaranteed compatibility with all EIA-310-E compliant 19" equipment. Its front and rear pairs of vertical rails are adjustable in quarter-inch increments from 4 to 37 inches. Adjustment is quick and an easy-view depth index ensures consistent rail placement without requiring time-consuming measurements. Each rack space within the enclosure is numbered for ready reference. Two of these adjustable vertical mounting rails support toolless button-mount 0U installation of up to four compatible PDUs and cable managers. This feature makes it easier to route cabling to rack equipment and reduces cord clutter.

The top panel of the SR42UBEXP is vented to help remove warm air from the enclosure and draw in cool air by convection. The top panel includes ports for cable routing, and can be quickly removed without tools. To facilitate cable access, the SR42UBEXP is open-bottom.

All components of the SR42UBEXP are grounded to the enclosure frame. Front and rear threaded grounding points are provided for connection to the facility earth ground. The removable front and rear doors feature quick-release ground wires.

To simplify deployment, the SR42UBEXP comes with preinstalled casters that enable it to be easily maneuvered into the desired location, where it can be secured by adjusting the preinstalled levelers. Note: the casters are intended for minor position adjustments and are not designed for moving the enclosure over long distances.

#### Features

- Ships fully assembled for rapid deployment and roll into place on heavy-duty pre-installed casters (casters are removable)
- Front and rear sets of equipment mounting rails adjust in 1/4" increments. Adjustment is quick and convenient. The easy-view depth index ensures consistent rail placement without requiring time-consuming measurements.
- Toolless accessory mounting rails (2 rails per enclosure) include slots for quick installation of compatible PDUs and vertical cable managers. Mounting slots are arranged in an industry-standard pattern compatible with a wide variety of accessories. Each rail can accommodate two vertical PDUs or cable managers side-by-side (four items per enclosure).
- Enclosure includes mounting hardware of 50 pieces of M6 cage nuts and 50 pieces of M6 screws
- Textured powder coat finish for tough resistance to environmental concerns such as deployment in warehouses.
- Massive front to rear ventilation capacity. 65+% open space in door perforation pattern meets or exceeds server manufacturer requirements.
- Maximum usable internal depth of 37 inches/94 cm (front to rear rail).
- Weight ratings of 3000 lb stationary and 2250 lb rolling.
- Front door is locking, reversible and removable.
- Rear doors are locking and reversible. Split rear door design reduces clearance requirements for service entry allowing the enclosure to be placed closer to a wall.
- Side panels can be added at a later time if needed. (p/n: SR42SIDE)

- Built in baying tabs allow enclosures to be combined securely in rows. Center-to-center width can be set at 600mm or 24" to match standard data center floor tiles.
- Leveling feet extend to allow enclosure to be positioned on uneven floors. Levelers are removable.
- Compact design allows the enclosure to roll through standard height commercial doorways.
- Convenient grounding system. All components are grounded to the enclosure frame which includes multiple connections for facility ground. Front and rear doors include quick-release ground wires.
- Open bottom for cable access.
- Top panel has generous cable access holes. Panel can be removed toollessly in seconds without having to disconnect cables first.
- Included stabilizing brackets are used for shipment and can be reattached at the bottom of the enclosure frame on the inside or outside of the rack.
- Compatibility with airflow optimization accessories as well as cable management accessories.

## Specifications

PHYSICAL	
Installed whole system maximum rack depth (inches)	37
Installed whole system maximum rack depth (cm)	94.0
Installed whole system minimum rack depth (inches)	4
Installed whole system total rack space height (rack spaces)	42U
Shipping weight (lbs)	226
Shipping weight (kg)	102.7
Shipping Dimensions (HWD/in)	84.5 x 27.75 x 47
Shipping Dimensions (HWD/cm)	214.63 x 70.48 x 91.44
Unit weight (lbs)	203
Unit weight (kg)	92
Unit Dimensions (cm)	199.39 x 60.02 x 109.22
Unit Dimensions (in)	EXTERNAL DIMENSIONS: 78.5 x 23.63 x 43 (HWD)
Color	Black
Weight Capacity - Stationary (lbs)	3000
Weight Capacity - Rolling (lbs)	2250
Units per Pallet	1
Installed whole system minimum rack depth (cm)	10.16
Weight Capacity - Stationary (kg)	1360.8
Weight Capacity - Rolling (kg)	1020.6
SPECIAL FEATURES	
Grounding lug	Front and Back door frames

CERTIFICATIONS	
Certifications	UL60950; RoHS; CE
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA/ECA-310-E
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
<a href="#">B020-U08-19-IP</a>	Console KVM Switch - 8-Port NetDirector 1U Rackmount Console IP KVM Switch w/17" LCD	1
<a href="#">B021-000-17</a>	Rackmount Console - 1U Rackmount Console with 17" LCD	1
<a href="#">B021-000-19</a>	Rackmount Console - 1U Rackmount Console with 19" LCD	1
<a href="#">B040-008-19</a>	NetController 19" VGA Console KVM Switch - 8 Port	1
<a href="#">B040-016-19</a>	NetController 19" VGA Console KVM Switch - 16 Port	1
<a href="#">N252-012</a>	12-Port Cat6 Patch Panel 568B	1
<a href="#">N252-024</a>	24-Port Cat6 Patch Panel 568B	1
<a href="#">N252-048</a>	48-Port Cat6 Patch Panel 568B	1
<a href="#">SRBOLTDOWN</a>	Bolt-Down Kit (Secures included stabilizing brackets or optional stabilizing plates to facility floor.)	1
<a href="#">SRCABLEDUCTVRT</a>	6-ft. (1.8 m) Vertical Cable Manager (Double finger duct with cover; toolless mounting.)	1
<a href="#">SRCABLEDUCT1U</a>	1U Horizontal Cable Manager (Finger duct with cover.)	1
<a href="#">SRCABLELADDER</a>	10-ft. x 1-ft. (3 m x 0.3 m) Cable Ladder (Includes 2 sections; requires SRCABLETRAY.)	1
<a href="#">SRCABLERINGVRT</a>	6-ft. (1.8 m) Vertical Cable Manager (Flexible ring type; toolless mounting.)	1
<a href="#">SRCABLERING1U</a>	1U Horizontal Cable Manager (Flexible ring type.)	1
<a href="#">SRCABLERING2U</a>	2U Horizontal Cable Manager (Flexible ring type.)	1
<a href="#">SRCABLETRAY</a>	Roof-Mounted Cable Trough (Provides cable routing and power/data cable segregation.)	1
<a href="#">SRCABLETRAYEXP</a>	Roof-Mounted Cable Trough Vertical Expansion (Requires SRCABLETRAY.)	1
<a href="#">SRCAGENUTS</a>	Square Hole Hardware Kit (Includes 50 M6 screws and washers.)	1
<a href="#">SRCOMBO</a>	Door Handles with Combination Lock (2-pack for front and rear doors; includes bypass key.)	1
<a href="#">SREXTENDER</a>	Rack Enclosure Extension Frame (Increases external depth of rack enclosures to 51-in. / 1295 mm; increases maximum mounting depth to 43.75-in. / 1111 mm.)	1
<a href="#">SRFANROOF</a>	Roof-Mounted Fan Panel, 120V (6 high-performance fans; 420 CFM; 5-15P plug; toolless mounting.)	1
<a href="#">SRFAN3U</a>	3U Fan Panel, 120V (3 high-performance fans; 210 CFM; 5-15P plug.)	1
<a href="#">SRSHELF2P</a>	2U Cantilever Fixed Shelf (60 lb / 27 kg capacity; 18-in. / 457 mm depth.)	1
<a href="#">SRSHELF4PHD</a>	Heavy-Duty Fixed Shelf (250 lb / 113 kg capacity; 26 in / 660 mm depth.)	1

SRSHELF4PKYBD	Keyboard Shelf (25 lb / 11 kg capacity; 16-in. / 406 mm depth.)	1
SRSHELF4PSL	Standard Sliding Shelf (50 lb / 22 kg capacity; 26 in / 660 mm depth.)	1
SRSHELF4PSLHD	Heavy-Duty Sliding Shelf (100 lb / 45 kg capacity; 26 in / 660 mm depth.)	1
SRSTABILIZE	Anti-Tip Stabilizing Plate Kit (Provides extra stability for standalone enclosures.)	1
SRSWITCH	Magnetic Door Switch Kit (2-pack for front and rear doors; requires ENVIROSENSE.)	1
SRXFANROOF	Roof-Mounted Fan Panel, 230V (6 high-performance fans; 420 CFM; C14 inlet; toolless mounting.)	1
SRXFAN3U	3U Fan Panel, 230V (3 high-performance fans; 210 CFM; C14 inlet.)	1
SR1UPANEL10	1U Blanking Panel Kit (10 pieces; toolless mounting.)	1
SR1UPANEL50	1U Blanking Panel Kit (50 pieces; toolless mounting.)	1
UPSHDEARKIT	Heavy-Duty Mounting Ear Kit (Supports 2U cabinets up to 65 lb / 29 kg from front vertical rails in 4-post or 2-post racks and enclosures. )	1
SR42SIDE	SmartRack side panel with key locking latch	1
N052-012	12-Port Cat5e Patch Panel 568B, 1U	1
N052-024	24-Port Cat5e Patch Panel 568B, 1U	1
N052-048	48-Port Cat5e Patch Panel 568B, 2U	1
N054-024	24 Port Cat5e Feedthrough Patch Panel	1
N250-024-LP	24-port Cat6 / Cat5e Low Profile Feed-through Wallmount Patch Panel 1U	1
N252-024-HU	24-Port Cat6 0.5U Patch Panel 568A/B	1
N252-024-V	24-Port Cat6 V-Shaped Patch Panel, 1U	1
N252-048-1U	48-Port Cat6 1U High Density 110 Type Patch Panel	1
N490-016-LCLC	16 Port Fiber Patch Panel, 1U (LC/LC)	1
N490-016-MTRJ	16 Port Fiber Patch Panel, 1U (MTRJ/MTRJ)	1
N490-016-SCSC	16 Port Fiber Patch Panel, 1U (SC/SC)	1
N490-016-STSC	16 Port Fiber Patch Panel, 1U (ST/SC)	1
N490-016-STST	16 Port Fiber Patch Panel, 1U (ST/ST)	1
SRPAGODAROOF	SmartRack Drip Resistant Roof	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.triplite.com/en/products/model.cfm?variables.txtModelID=3216](http://www.triplite.com/en/products/model.cfm?variables.txtModelID=3216).

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.