

Product information

RS2-TX

Industrial Ethernet:Entry Level Hubs And Switches:Unmanaged Standard Rail Switches:RS2-TX

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49855-50103-34221/en/conf/uistate>

Name	RS2-TX
	
	Unmanaged Industrial ETHERNET Rail Switch, store and forward switching mode, Ethernet (10 Mbit/s) and Fast-Ethernet (100 Mbit/s)
Delivery informations	
Availability	available
Product description	
Description	Unmanaged Industrial ETHERNET Rail Switch, store and forward switching mode, Ethernet (10 Mbit/s) and Fast-Ethernet (100 Mbit/s)
Port type and quantity	8 x 10/100Base-TX, TP cable, RJ45 sockets, auto-crossing, auto-negotiation, auto-polarity
Type	RS2-TX
Order No.	943 686-003
More Interfaces	
Power supply/signaling contact	1 plug-in terminal block, 5-pin
Network size - length of cable	
Twisted pair (TP)	0 - 100 m
Network size - cascading	
Line - / star topology	any
Power requirements	
Operating voltage	24 V DC (-25% to +30%)
Current consumption at 24 V DC	max. 290 mA
Power consumption	max. 7,0 W at 24 V DC
Service	
Diagnostics	LEDs (power, link status, data, error), signal contact / fault relays (24 V DC / 1 A)
Redundancy	
Redundancy functions	redundant 24 V power supply
Ambient conditions	
Operating temperature	0°C to +60°C
Storage/transport temperature	-25 °C to +70 °C
Relative humidity (non-condensing)	10% to 95%
MTBF	61 years; MIL-HDBK 217F: Gb 25 °C
Mechanical construction	
Dimensions (W x H x D)	47 mm x 135 mm x 111 mm
Mounting	DIN Rail 35 mm
Weight	230 g
Protection class	IP20
Mechanical stability	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	1 mm, 2 Hz - 13.2 Hz, 90 min.; 0.7g, 13.2 Hz - 100 Hz, 90 min.; 3.5 mm, 3 Hz - 9 Hz, 10 cycles, 1 octave/min.; 1g, 9 Hz - 150 Hz, 10 cycles, 1 octave/min.
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	6 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80 - 1000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line
EN 61000-4-6 conducted immunity	3 V (10 kHz - 150 kHz), 10 V (150 kHz - 80 MHz)
EMC emitted immunity	
FCC CFR47 Part 15	FCC CFR47 Part 15 Class A
EN 55022	EN 55022 Class A

Industrial Ethernet:Entry Level Hubs And Switches:Unmanaged Standard Rail Switches:RS2-TX
<http://www.e-catalog.beldensolutions.com/link/57078-24455-49855-50103-34221/en/conf/ui/state>
Approvals

Safety of industrial control equipment	cUL 508 (pending)
Hazardous locations	cUL 1604 Class1 Div 2 (pending)
Safety of information technology equipment	cUL 60950-1 (pending)
Shipbuilding	Germanischer Lloyd

Scope of delivery and accessories

Scope of delivery	device, terminal block, operating manual
Accessories to order separately	rail power supply RPS 30, RPS 80 EEC or RPS 120 EEC, 19" installation frame

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.