



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SR42UW

42U White SmartRack Premium Enclosure (includes doors and side panels)



Highlights

- 42U White SmartRack enclosure with doors and side panels
- 4 interior vertical posts with unthreaded square hole openings
- Standard 24" (600mm) width and 42" (1050mm) depth for optimizing floor space
- Ships fully assembled
- Massive front to rear ventilation capacity
- 3000 lb stationary / 2250 lb rolling load capacity
- Locking, removable, reversible front and rear doors
- Locking, removable side panels keyed alike with doors
- Pre-installed casters and leveling feet
- Rolls through standard 7 foot doorway
- Includes 50 pieces of M6 cage nuts and 50 pieces of M6 screws (equipment mounting hardware)
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

Description

The SR42UW features a massive front-to rear-ventilation capacity that meets or exceeds server manufacturer requirements. Its integrated baying tabs make it easy to combine multiple enclosures in rows for data center applications. This enclosure is also compatible with hot-aisle/cold-aisle configurations.

The SR42UW houses 3000 lb of standard 19-inch rack equipment in 42U. Its front and rear pairs of vertical rails have square mounting holes that are adjustable in quarter-inch increments from 4 to 37 inches. Adjustment is quick and an easy-view depth index ensures consistent rail placement without requiring time-consuming measurements. Each rack space within the enclosure is numbered for ready reference.

Two of the adjustable vertical mounting rails support toolless button-mount 0U installation of up to four compatible PDUs and cable managers. This feature makes it easier to route cabling to rack equipment and reduces cord clutter.

With its locking, reversible, removable front and rear doors, and locking, removable side panels, the SR42UW provides ultimate equipment safety. The side panels are half size for ease of removal and reinstallation. The split rear door design allows the enclosure to be placed closer to a wall. The SR42UW meets all requirements toward PCI DSS compliance.

The top panel of the SR42UW is vented to help remove warm air from the enclosure and draw in cool air by convection. The top panel includes ports for cable routing, and can be quickly removed without tools. To facilitate cable access, the SR42UW is open-bottom.

All components of the SR42UW are grounded to the enclosure frame. Front and rear threaded grounding points are provided for connection to the facility earth ground. The removable front and rear doors feature quick-release ground wires.

To simplify deployment, the SR42UW comes with preinstalled casters that enable it to be easily maneuvered into the desired location, where it can be secured by adjusting the preinstalled levelers. Note: the casters are intended for minor position adjustments and are not designed for moving the enclosure over long distances.

The SR42UW comes with a 5-year product warranty. As part of the SmartRack family, the SR42UW is compatible with Tripp Lite's extensive range of rackmount accessories, enabling you to customize your solution to meet any requirement.

Package Includes

- SR42UW Rack Enclosure
- (4) side panels
- (4) side panel locks
- (2) door & side panel keys

- (50) M6 screws
- (50) M6 washers
- (50) M6 cage nuts
- Owner's Manual

Features

- White version of our standard 42U rack enclosure offers easier visibility of installed equipment
- Ships fully assembled for rapid deployment and roll into place on heavy-duty pre-installed casters (casters are removable)
- Front and rear sets of equipment mounting rails adjust in 1/4" increments. Adjustment is quick and convenient. The easy-view depth index ensures consistent rail placement without requiring time-consuming measurements.
- Toolless accessory mounting rails (2 rails per enclosure) include slots for quick installation of compatible PDUs and vertical cable managers. Mounting slots are arranged in an industry-standard pattern compatible with a wide variety of accessories. Each rail can accommodate two vertical PDUs or cable managers side-by-side (four items per enclosure).
- Enclosure includes mounting hardware of 50 pieces of M6 cage nuts and 50 pieces of M6 screws
- Textured powder coat finish for tough resistance to environmental concerns such as deployment in warehouses.
- Massive front to rear ventilation capacity. 65+% open space in door perforation pattern meets or exceeds server manufacturer requirements.
- Maximum usable internal depth of 37 inches/94 cm (front to rear rail).
- Weight ratings of 3000 lb stationary and 2250 lb rolling.
- Front door is locking, reversible and removable.
- Rear doors are locking and reversible. Split rear door design reduces clearance requirements for service entry allowing the enclosure to be placed closer to a wall.
- Locking removable side panels are 'half size' to make them smaller and lighter improving ease of installation and servicing. Two side panels per side (4 panels total). Side panels are keyed alike to the front and rear doors.
- Built in baying tabs allow enclosures to be combined securely in rows. Center-to-center width can be set at 600mm or 24" to match standard data center floor tiles.
- Leveling feet extend to allow enclosure to be positioned on uneven floors. Levelers are removable.
- Compact design allows the enclosure to roll through standard height commercial doorways.
- Convenient grounding system. All components are grounded to the enclosure frame which includes multiple connections for facility ground. Front and rear doors include quick-release ground wires.
- Open bottom for cable access.
- Top panel has generous cable access holes. Panel can be removed toollessly in seconds without having to disconnect cables first.
- Included stabilizing brackets are used for shipment and can be reattached at the bottom of the enclosure frame on the inside or outside of the rack.
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance
- Compatibility with airflow optimization accessories as well as cable management accessories.

Specifications

PHYSICAL	
Installed whole system maximum rack depth (inches)	37
Installed whole system maximum rack depth (cm)	94.0
Installed whole system minimum rack depth (inches)	4
Installed whole system total rack space height (rack spaces)	42U
Shipping weight (lbs)	336
Shipping weight (kg)	152
Shipping Dimensions (HWD/in)	85 x 26 x 45
Shipping Dimensions (HWD/cm)	215.9 x 66.04 x 114.3

Unit weight (lbs)	286
Unit weight (kg)	130
Unit Dimensions (cm)	199.39 x 60.02 x 109.22
Unit Dimensions (in)	EXTERNAL DIMENSIONS: 78.5 x 23.63 x 43 (HWD)
Color	White
Weight Capacity - Stationary (lbs)	3000
Weight Capacity - Rolling (lbs)	2250
Units per Pallet	1
Weight Capacity - Stationary (kg)	1360.8
Weight Capacity - Rolling (kg)	1020.6
SPECIAL FEATURES	
Grounding lug	Front and back door frames
CERTIFICATIONS	
Certifications	UL60950; RoHS, CE
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA/ECA-310-E
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
SRBOLTDOWN	Bolt-Down Kit (Secures included stabilizing brackets or optional stabilizing plates to facility floor.)	1
SRCABLEDUCTVRT	6-ft. (1.8 m) Vertical Cable Manager (Double finger duct with cover; toolless mounting.)	1
SRCABLEDUCT1U	1U Horizontal Cable Manager (Finger duct with cover.)	1
SRCABLELADDER	10-ft. x 1-ft. (3 m x 0.3 m) Cable Ladder (Includes 2 sections; requires SRCABLETRAY or SRLADDERATTACH)	1
SRCABLERINGVRT	6-ft. (1.8 m) Vertical Cable Manager (Flexible ring type; toolless mounting.)	1
SRCABLERING1U	1U Horizontal Cable Manager (Flexible ring type.)	1
SRCABLERING2U	2U Horizontal Cable Manager (Flexible ring type.)	1
SRCABLETRAY	Roof-Mounted Cable Trough (Provides cable routing and power/data cable segregation.)	1
SRCABLETRAYEXP	Roof-Mounted Cable Trough Vertical Expansion (Requires SRCABLETRAY.)	1
SRCAGENUTS	Square Hole Hardware Kit (Includes 50 M6 screws and washers.)	1
SRCOMBO	Door Handles with Combination Lock (2-pack for front and rear doors; includes bypass key.)	1

SRFANROOF	Roof-Mounted Fan Panel, 120V (6 high-performance fans; 630 CFM; 5-15P plug; toolless mounting)	1
SRFAN3U	3U Fan Panel, 120V (3 high-performance fans; 210 CFM; 5-15P plug.)	1
SRSHELF2P	2U Cantilever Fixed Shelf (60 lb / 27 kg capacity; 18-in. / 457 mm depth.)	1
SRSHELF4PHD	Heavy-Duty Fixed Shelf (250 lb / 113 kg capacity; 26 in / 660 mm depth.)	1
SRSHELF4PKYBD	Keyboard Shelf (25 lb / 11 kg capacity; 16-in. / 406 mm depth.)	1
SRSHELF4PSL	Standard Sliding Shelf (50lb / 23 kg capacity; 28 1/4 in/ 660 mm depth.)	1
SRSHELF4PSLHD	Heavy-Duty Sliding Shelf (200 lb / 91 kg capacity; 26 in / 660 mm depth.)	1
SRSTABILIZE	Anti-Tip Stabilizing Plate Kit (Provides extra stability for standalone enclosures.)	1
SRSWITCH	Magnetic Door Switch Kit for front and rear doors; requires ENVIROSENSE	1
SRXFANROOF	Roof-Mounted Fan Panel, 208-240V (6 high-performance fans; 420 CFM; C14 inlet; toolless mounting.)	1
SRXFAN3U	3U Fan Panel, 230V (3 high-performance fans; 315 CFM; C14 inlet.)	1
SR1UPANEL10	1U Blanking Panel Kit (10 pieces; toolless mounting.)	1
SR1UPANEL50	1U Blanking Panel Kit (50 pieces; toolless mounting.)	1
UPSHDEARKIT	Heavy-Duty 2-post Front Mounting Ear Kit	1
SRVRTBAR	Vertical Cable Management Bars	1
SRFILTER	Filter Kit for SmartRack Enclosures	1
SRTHERMDUCT	SmartRack Thermal Duct Kit for SmartRack Enclosures	1
4POSTRAILKIT1U	1U Universal Adjustable Rackmount Shelf Kit	1
SRCASTERHDKIT	Heavy-Duty Rolling Caster Kit (includes 4 casters)	1
SRHALFRAIL	21U Half Rail Accessory	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?variables.txtModelID=5311.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.