


1370R Coax - System Integrators Video Cable



For more Information
please call

1-800-Belden1

**General Description:**

20 AWG solid .032" bare copper conductor, gas-injected foam HDPE insulation, Duobond® II plus tinned copper braid shield (85% coverage), PVC jacket.

Usage (Overall)

Suitable Applications: Commercial Video

Physical Characteristics (Overall)**Conductor**

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	Solid	BC - Bare Copper	0.8128

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	3.454

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duobond® II	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100.000
2		Braid	TC - Tinned Copper	85.000

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 5.131 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +75°C
UL Temperature Rating:	75°C
Bulk Cable Weight:	32.740 Kg/Km
Max. Recommended Pulling Tension:	204.617 N
Min. Bend Radius/Minor Axis:	50.800 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMR
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes

1370R Coax - System Integrators Video Cable

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	11/21/2011
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
RG Type:	59/U

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
----------------	-----------------------

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	No

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1370P

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (μH/m)
0.351067

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
54.465

Nominal Velocity of Propagation:

VP (%)
84.000

Nominal Delay:

Delay (ns/m)
3.970

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
33.138

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
13.452

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1.000	0.984
3.600	1.969
5.000	2.067
6.000	2.264
7.000	2.428
10.000	2.953
12.000	2.986
25.000	4.265
67.500	6.726

1370R Coax - System Integrators Video Cable

71.500	6.890
88.500	7.218
100.000	7.546
135.000	8.859
143.000	9.187
180.000	10.171
270.000	12.468
360.000	14.436
540.000	18.046
720.000	20.998
750.000	21.327
1000.000	24.936
1500.000	30.513
2000.000	35.763
2250.000	38.060
3000.000	43.965

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1:

Impedance tested in accordance with ASTM D-4566 paragraph 48.2, option 2 using a 75 Ohm fixed bridge and termination. 75 +/- 1.5 Ohms

Other Electrical Characteristic 2:

Return Loss tested in accordance with ASTM D-4566 paragraph 50.3, using a 75 Ohm fixed bridge and termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5.000	3000.000	15.000

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1370R N3U1000	305 MT	10.886 KG	GREEN, MIL		#20 PE/GIFHDLDP SH PVC
1370R N3U500	152 MT	5.670 KG	GREEN, MIL		#20 PE/GIFHDLDP SH PVC
1370R 0011000	305 MT	10.886 KG	BROWN		#20 PE/GIFHDLDP SH PVC
1370R 001500	152 MT	5.670 KG	BROWN		#20 PE/GIFHDLDP SH PVC
1370R 0021000	305 MT	10.886 KG	RED		#20 PE/GIFHDLDP SH PVC
1370R 002500	152 MT	5.670 KG	RED		#20 PE/GIFHDLDP SH PVC
1370R 0031000	305 MT	10.886 KG	ORANGE		#20 PE/GIFHDLDP SH PVC
1370R 003500	152 MT	5.670 KG	ORANGE		#20 PE/GIFHDLDP SH PVC
1370R 0041000	305 MT	10.886 KG	YELLOW		#20 PE/GIFHDLDP SH PVC
1370R 004500	152 MT	5.670 KG	YELLOW		#20 PE/GIFHDLDP SH PVC
1370R 0061000	305 MT	10.886 KG	BLUE, LIGHT		#20 PE/GIFHDLDP SH PVC
1370R 006500	152 MT	5.670 KG	BLUE, LIGHT		#20 PE/GIFHDLDP SH PVC
1370R 0071000	305 MT	10.886 KG	VIOLET		#20 PE/GIFHDLDP SH PVC
1370R 007500	152 MT	5.670 KG	VIOLET		#20 PE/GIFHDLDP SH PVC
1370R 0081000	305 MT	10.886 KG	GRAY		#20 PE/GIFHDLDP SH PVC
1370R 008500	152 MT	5.670 KG	GRAY		#20 PE/GIFHDLDP SH PVC
1370R 0091000	305 MT	10.886 KG	WHITE		#20 PE/GIFHDLDP SH PVC
1370R 009500	152 MT	5.670 KG	WHITE		#20 PE/GIFHDLDP SH PVC
1370R 0101000	305 MT	10.886 KG	BLACK		#20 PE/GIFHDLDP SH PVC
1370R 010500	152 MT	5.670 KG	BLACK		#20 PE/GIFHDLDP SH PVC

Revision Number: 2 Revision Date: 05-31-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or

1370R Coax - System Integrators Video Cable

exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.