


THIS DRAWING HAS BEEN GENERATED
AND IS MAINTAINED BY A CAD SYSTEM.
CHANGES SHALL ONLY BE
INCORPORATED AS DIRECTED BY THE
DESIGN ACTIVITY.

THESE COMMODITIES, TECHNOLOGY OR
SOFTWARE WERE EXPORTED FROM THE
UNITED STATES IN ACCORDANCE WITH THE
EXPORT ADMINISTRATION REGULATIONS.
DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

REVISIONS

LTR	DESCRIPTION	ECO NUM.	DATE	APPROVED
A	UPDATE CONNECTIONS	2180	4/5/99	
B	UPDATE CONNECTORS	2237	5/17/99	JAH
C	UPDATE OPERATING TEMP	7746	12/3/08	DWR
D	UPDATE COMPONENT VIEW	10444	2/13/12	LC



UNLESS
OTHERWISE
SPECIFIED DIM.
IN INCHES
BEFORE
PLATING

DRAWN:

JDW

DATE

3/15/99

CHECKED:

CKW

5/24/99

ENGR. APPD:

JAH

5/25/99

PROJ. APPD:

DLR

5/24/99

MATERIAL:

NOTED

APPROVED:



©2009 Transector Systems, Inc. All rights reserved.

10701 Airport Drive, Hayden, ID 83835, USA

+1.208.772.8515 FAX +1.208.762.6034

800.882.9110 www.transector.com

TITLE:

**FSP 4003 MC
SPECIFICATION**

NOTICE: THE INFORMATION
AND DESIGN CONTAINED HEREIN IS
THE PROPERTY OF TRANSECTOR
SYSTEMS. WHO RESERVES ALL
RIGHTS THERETO

SIZE

A

CAGE

30992

DRAWING NUMBER

1400-321-3

REV

D


SCALE = N/A

PAGE 1 OF 3

SURGE SUPPRESSOR Model: FSP 4003 MC

1. **GENERAL DESCRIPTION:** The FSP 4003 MC surge suppressor is a high-speed, high-current solid state device designed to protect RS 422, 4-20 ma Double Wire Pair (4-Wire) configurations and other balanced pair applications from transient over voltages. **The FSP 4003 MC uses only silicon suppression components.** It connects to the equipment and line via two (2), six (6) position terminal blocks.
2. **PERFORMANCE REQUIREMENTS:**
 - 2.1. **Electrical Service:**
 - 2.1.1. **Service Voltage**.....52 VDC
 - 2.1.2. **Configuration** 2 balanced pairs + 2 shields
 - 2.1.3. **Input Connection** Terminal Blocks
 - 2.1.3.1. **Number of connector positions**6 in 6 out
 - 2.1.4. **Protection Modes** Line to Line, Line to GND (No protection on shield)
 - 2.1.5. **Maximum Continuous Operating Voltage**.....54 VDC
 - 2.2. **Electrical Performance:**
 - 2.2.1. **Testing:**
 - 2.2.1.1. Tested to IEEE 10/1000
 - 2.2.1.1.1. Long WaveIpk 67 A peak
 - 2.2.2. **Response Time (Max)**5 nanoseconds
 - 2.2.3. **Standby Power (Max)**< 0.05 Watt
 - 2.2.4. **Operating Temperature**.....-40°C to +65°C
 - 2.3. **Mechanical:**
 - 2.3.1. **Enclosure Description:** The suppressor is housed in a molded plastic enclosure that is 2.2 in long, 2.2 in wide and 0.9 in tall.
3. **ENVIRONMENTAL:**
 - 3.1. **Operating Temperature:**-40°C to +65°C
 - 3.2. **Storage Temperature:**-40°C to +65°C
 - 3.3. **Relative Humidity:**90%

4. MECHANICAL DETAIL



ALL DIMENSIONS NOMINAL

