

Cushion-Grip Screwdrivers

Miniature Cushion-Grip Screwdrivers



608-6

Additional Feature:

- Precision tip for exact fit and rigorous applications.

Cat. No.	Tip Type	Shank Tip Size	Shank Length	Overall Length	Weight (lbs.)
604-3	Phillips	No. 0	3" (76 mm)	5-3/4" (146 mm)	.04
606-2	keystone	1/16" (1.6 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
607-2	cabinet	3/32" (2.4 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
607-3	cabinet	3/32" (2.4 mm)	3" (76 mm)	5-3/4" (146 mm)	.04
607-4	cabinet	3/32" (2.4 mm)	4" (102 mm)	6-3/4" (171 mm)	.04
608-2	cabinet	1/8" (3.2 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
608-3	cabinet	1/8" (3.2 mm)	3" (76 mm)	5-3/4" (146 mm)	.04
608-4	cabinet	1/8" (3.2 mm)	4" (102 mm)	6-3/4" (171 mm)	.05
608-6	cabinet	1/8" (3.2 mm)	6" (152 mm)	8-3/4" (222 mm)	.05
608-8	cabinet	1/8" (3.2 mm)	8" (203 mm)	10-3/4" (273 mm)	.05
608-10	cabinet	1/8" (3.2 mm)	10" (254 mm)	12-3/4" (324 mm)	.05

Coated Cabinet-Tip Screwdrivers – Round-Shanks



620-4

Additional Features:

- Plastic coated for circuit protection only. **NOT INSULATED.**
- Special plastic coating resists cutting, cracking and chipping.
- Thin coating permits use in confined areas.

Cat. No.	Shank Tip Width	Shank Length	Overall Length	Weight (lbs.)
620-3	3/16" (5 mm)	3" (76 mm)	6-3/4" (171 mm)	.15
621-6	3/16" (5 mm)	6" (152 mm)	9-3/4" (248 mm)	.20
621-8	3/16" (5 mm)	8" (203 mm)	11-3/4" (298 mm)	.20
621-10	3/16" (5 mm)	10" (254 mm)	13-3/4" (349 mm)	.25
Heavy-Duty Shanks				
620-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.20
620-6	5/16" (8 mm)	6" (152 mm)	10-15/16" (278 mm)	.40
620-8	3/8" (10 mm)	8" (203 mm)	13-7/16" (341 mm)	.60

Square-Recess Tip Screwdrivers – Round-Shanks



660

Additional Features:

- Color-coded handle ends for quick and easy identification.
- Round shank with square-recess tip.
- Chrome plated shank for corrosion resistance.

Cat. No.	Point Size	Color Code	Shank Length	Overall Length	Weight (lbs.)
660	No. 0	yellow	4" (102 mm)	7-3/4" (197 mm)	.20
661	No. 1	green	4" (102 mm)	7-3/4" (197 mm)	.20
662	No. 2	red	4" (102 mm)	8-1/4" (210 mm)	.30
663	No. 3	black	4" (102 mm)	8-1/4" (210 mm)	.30
665	No. 1	green	8" (203 mm)	11-3/4" (298 mm)	.30
666	No. 2	red	8" (203 mm)	12-1/4" (311 mm)	.40
667	No. 3	black	8" (203 mm)	12-1/4" (311 mm)	.40

Refer to the insulated section for insulated screwdrivers.

TORX® Screwdrivers – Round-Shanks



19544

Additional Features:

- Color-coded handle ends for quick and easy identification.
- TORX® tip drive cuts slippage, saves fasteners and transmits more torque to the work.
- Chrome-plated shank for corrosion resistance.

Cat. No.	TORX® Size	Color Code	Shank Length	Overall Length	Weight (lbs.)
19542	T15	yellow	4" (102 mm)	8-5/16" (211 mm)	.20
19543	T20	green	4" (102 mm)	8-5/16" (211 mm)	.25
19544	T25	blue	4" (102 mm)	8-5/16" (211 mm)	.25
19545	T27	brown	4" (102 mm)	8-5/16" (211 mm)	.25
19546	T30	red	4" (102 mm)	8-5/16" (211 mm)	.25

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

All dimensions are in inches and (millimeters).

▲WARNING: Always wear approved eye protection.

▲WARNING: NOT insulated. Will NOT protect against electrical shock.

▲WARNING: Do NOT use to pry or chisel.

