

# SNC-ZB550

Hybrid Fixed HD Camera

**SONY**  
make.believe

## High-quality 720p HD Hybrid Fixed Camera

- IPELA HYBRID™ — Sony IP and analog-over-coax technology\*1
- Excellent 720p HD picture quality, supporting H.264 at 30 fps (IP)
- 1.3 megapixel (1280 x 1024) maximum resolution (IP)
- Three codecs (H.264, MPEG-4, JPEG) and dual streaming capability\*4



**HD** **1.3M**  
HIGH RESOLUTION

### Key Features

- Simultaneous transmission of IP HD video and analog SD video\*2
  - Maximum cable length of 1,000 feet (300 m) with an RG-59 coaxial cable\*3
  - The Exmor™ CMOS sensor delivers high quality images with low noise
- Exmor™**
- Easy Focus - allows installer/user to focus the camera remotely or locally
  - True Day/Night function to switch to Day or Night mode depending on the light level
  - Smartphone viewer for accessing the camera from a smartphone

- DEPA™ Intelligent Video Analytics enables cameras to send not only video images, but related metadata, including object data (size and position) to the DEPA-enabled recorder. Since part of the image processing is done on the camera side, the load to the recorder can be reduced enabling camera expansion



- ONVIF (Open Network Video Interface Forum) Version 1.02 software that ensures greater interoperability and more flexibility in building multiple-vendor systems



\*1 Sony IP and analog-over-coax technology is developed based on Intersil's SLOC™ (Security Link Over Coax) technology.

\*2 For output of IP and analog signals from its SLOC port, the camera must be connected to a SLOC-compatible device via a coaxial cable. The output analog image may not display correctly, depending on the video format and image size settings. For details please contact your nearest Authorized Sony Reseller.

\*3 Cable length varies according to cable grade and quality.

\*4 Dual streaming is only available when SLOC is OFF.


**IPELA HYBRID** **sloc**

## SPECIFICATIONS


SNC-ZB550	
<b>Camera</b>	
Image sensor	1/3-type Exmor CMOS sensor
Number of effective pixels	Approx. 1.4 Megapixel (1329 x 1049)
Signal system	NTSC color system/PAL color system (switchable)
Minimum illumination	Color: 0.50 lx, B/W: 0.30 lx (F1.2, shutter 1/30 s, AGC 42 dB, 50 IRE (1P))
Gain	Auto (set Max limit value)
Shutter speed	1/1 s to 1/10,000 s
Exposure control	Backlight compensation, Exposure compensation, AGC, Shutter speed
White balance	ATW, ATW-PRO, Fluorescent lamp, Mercury lamp, Sodium vapour lamp, Metal halide lamp, White LED, One push WB, Manual
Lens	CS mount vari-focal lens
Zoom ratio	Optical 2.9x
Horizontal viewing angle	96.5° to 33.9°
Focal length	f = 2.8 mm to 8.0 mm
F-number	F1.2 (Wide), F1.9 (Tele)
Minimum object distance	300 mm
<b>Camera Features</b>	
Day/Night	Yes, true Day/Night
Wide-D	No
Noise reduction	Yes
<b>Image</b>	
Codec image size (H x V)	1280 x 1024, 1280 x 960, 1280 x 800, 1280 x 720, 1024 x 768, 1024 x 576, 800 x 600, 800 x 480, 768 x 576, 720 x 576, 720 x 480, 704 x 576, 640 x 480, 640 x 368, 384 x 288, 320 x 240, 320 x 192
Video compression format	H.264, MPEG-4, JPEG
Codec streaming capability	Dual streaming*1 (Any combination with H.264/MPEG-4/JPEG, including multiple streams of the same format)
Maximum frame rate	30 fps (H.264, MPEG-4, JPEG) at 1280 x 720
Composite video output	Yes, when SLOC switch is OFF
<b>Scene Analytics</b>	
Intelligent motion detection	Yes
<b>Network</b>	
Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, FTP (client only), SMTP, DHCP, DNS, NTP, RTP/RTCP, RTSP, SNMP (MIB-2)
ONVIF software	Yes (version 1.02)
Number of clients	5
Authentication	IEEE802.1X
<b>Interface</b>	
Video out (SLOC OFF)	BNC x1 (Video out: 1.0 Vp-p, 75 ohms, unbalanced, sync negative)
Network port	10BASE-T/100BASE-TX (RJ-45)
Sensor input	x1, make contact, break contact
Alarm output	x1, 24 V AC/DC, 1 A (mechanical relay outputs electrically isolated from the camera)
Microphone input	No
Card slots	No
<b>System Requirements</b>	
Operating system	Microsoft Windows XP® (32 bit), Windows Vista® (32 bit), Windows 7® (32 bit/64 bit)
Processor	Intel Core2 Duo 2 GHz or higher
Memory	1 GB or more
Web browser	Microsoft Internet Explorer® Ver. 6.0, Ver. 7.0, Ver. 8.0 Firefox® Ver. 3.5 (plug-in free viewer only) Safari® Ver. 4.0 (Plug-in free viewer only) Google® Chrome Ver. 4.0 (plug-in free viewer only)
<b>General</b>	
Power requirements	AC 24 V, DC 12 V
Power consumption	6.0 W max.
Operating temperature	14 °F to 122 °F (-10 °C to +50 °C)
Starting temperature	32 °F to 122 °F (0 °C to +50 °C)
Storage temperature	-4 °F to +140 °F (-20 °C to +60 °C)
Operating humidity	20% to 80%
Storage humidity	20% to 95%
Vandal resistant	No
Dimensions (W x H x D)	2 7/8 inches x 2 1/2 inches x 5 3/4 inches (72 mm x 63 mm x 145 mm) not including the projecting parts 2 7/8 inches x 2 1/2 inches x 7 7/8 inches (72 mm x 63 mm x 197 mm) with lens not including the projecting parts
Weight	Approx. 1 lb 3.4 oz (550 g) with lens
Safety regulations	JATE technical standard (LAN), UL2044, IEC60950-1 (CB) VCCI (Class A), FCC (Class A), IC (Class A) Emission: EN55022 (Class A) + EN50130-4 Immunity: EN55022 (Class A) + EN55024 Emission: AS/NZS CISPR22 (Class A)
Supplied accessories	CD-ROM (Users guides, and supplied programs) (1), Wire rope (1), Screw M4 (1), DC 12 V/AC 24 V connector (1), Installation manual (1 set)

\*1 Dual streaming is not available when an analog video signal is output from the SLOC port.

## SYSTEM CONFIGURATION



## DIMENSIONS



## REAR PANEL

