MIC® Tight-Buffered Cable, Riser

6 F, 50 µm multimode (OM2)

CORNING

Corning Cable Systems MIC[®] Riser Cables are designed for use in riser and general purpose environments for intrabuilding backbone and horizontal installations. These multifiber cables use 900 µm TBII[®] Buffered Fibers to enable easy, consistent stripping and facilitate termination. The fibers are surrounded by dielectric strength members and protected by a flame-retardant outer jacket.

The all-dielectric cable construction requires no grounding or bonding. MIC Plenum cables are ideal for routing inside buildings, within plenum areas and riser shafts, to the telecommunications rooms and workstations. The MIC Plenum Cables meet the application requirements of the National Electrical Code[®] (NEC[®]) Article 770 and are OFNP and FT-6 listed.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

Features and Benefits

900 µm TBII® Buffered Fibers Easy, consistent stripping


All-dielectric construction Requires no grounding or bonding

Flame-retardant jacket Rugged and durable

Standards

Approval and Listings	National Electrical Code® (NEC®) OFNR, CSA FT-4, ICEA S-83-596
Flame Resistance	UL-1666 (for riser and gen- eral building applications)





MIC® Tight-Buffered Cable, Riser

6 F, 50 μm multimode (OM2)

CORNING

Specifications

General Specifications	
Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser
Cable Type	Tight-Buffered
Product Type	Distribution
Flame Rating	Riser (OFNR)
Fiber Category	50 µm MM (OM2)

Temperature Range	
Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-20 °C to 70 °C (-4 °F to 158 °F)

Yarn
6
Blue, Orange, Green, Brown, Slate, White
Dielectric strength members
1
Flame-retardant
Orange

Mechanical Characteristics Cable	
Max. Tensile Strengths, Short-Term	660 N (150 lbf)
Max. Tensile Strengths, Long-Term	200 N (45 lbf)
Nominal Outer Diameter	5.5 mm (0.22 in)
Weight	26 kg/km (17 lb/1000 ft)
Min. Bend Radius Installation	83 mm (3.3 in)
Min. Bend Radius Operation	28 mm (1.1 in)



MIC® Tight-Buffered Cable, Riser

6 F, 50 μm multimode (OM2)

CORNING

Fiber Specifications

Optical Characteristics (cabled)	
Fiber Type	Multimode
Fiber Core Diameter	50 µm
Fiber Category	OM2
Fiber Code	Т
Performance Option Code	31
Wavelengths	850 nm / 1300 nm
Maximum Attenuation	2.8 dB/km / 1 dB/km
Min. Overfilled Launch (OFL) Bandwidth	700 MHz*km / 500 MHz*km
Minimum Effective Modal Bandwidth (EMB)	950 MHz*km / -
Serial 1 Gigabit Ethernet	750 m / 600 m
Serial 10 Gigabit Ethernet	150 m / -

Notes: 1) 50 μ m multimode fiber macrobend loss \leq 0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.

2) Improved attenuation and bandwidth options available.3) Bend-insensitive single-mode fibers available on request.

4) Contact a Corning Cable Systems Customer Care Representative for additional information.

Ordering Information

Part Number	006T81-31131-24
Product Description	MIC^{\circledast} Tight-Buffered Cable, Riser, 6 F, 50 μm multimode (OM2)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks. Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

