

MIC[®] Tight-Buffered Cable, Riser

24 F, Single-mode (OS2)

CORNING

Corning Cable Systems MIC[®] Riser Cables are designed for use in riser and general purpose environments for intrabuilding backbone and horizontal installations. These multifiber cables use 900 μm TBII[®] Buffered Fibers to enable easy, consistent stripping and facilitate termination. The fibers are surrounded by dielectric strength members and protected by a flame-retardant outer jacket.

The all-dielectric cable construction requires no grounding or bonding. MIC Plenum cables are ideal for routing inside buildings, within plenum areas and riser shafts, to the telecommunications rooms and workstations. The MIC Plenum Cables meet the application requirements of the National Electrical Code[®] (NEC[®]) Article 770 and are OFNP and FT-6 listed.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.



Features and Benefits

900 μm TBII[®] Buffered Fibers


Easy, consistent stripping

All-dielectric construction

Requires no grounding or bonding

Flame-retardant jacket

Rugged and durable



Standards

Approval and Listings

National Electrical Code[®]
(NEC[®]) OFNR, CSA FT-4,
ICEA S-83-596

Flame Resistance

UL-1666 (for riser and general building applications)

CORNING

MIC[®] Tight-Buffered Cable, Riser

24 F, Single-mode (OS2)

CORNING

Specifications

General Specifications	
Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser
Cable Type	Tight-Buffered
Product Type	Distribution
Flame Rating	Riser (OFNR)
Fiber Category	Single-mode (OS2)

Temperature Range	
Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-20 °C to 70 °C (-4 °F to 158 °F)

Cable Design	
Central Element	Yarn
Fiber Count	24
Tight Buffer Color	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Tight Buffer Color, Layer 2	Violet, Rose, Aqua, Blue*, Orange*, Green*, Brown*, Slate*, White*, Red*, Black*, Yellow*, Violet*, Rose*, Aqua*
Tensile Strength Elements and/or Armoring - Layer 2	Dielectric strength members
Number of Ripcords	1
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Yellow

Mechanical Characteristics Cable	
Max. Tensile Strengths, Short-Term	660 N (150 lbf)
Max. Tensile Strengths, Long-Term	200 N (45 lbf)
Nominal Outer Diameter	8 mm (0.31 in)
Weight	56 kg/km (39 lb/1000 ft)
Min. Bend Radius Installation	120 mm (4.7 in)
Min. Bend Radius Operation	80 mm (3.1 in)

MIC[®] Tight-Buffered Cable, Riser

24 F, Single-mode (OS2)



Fiber Specifications

Optical Characteristics (cabled)	
Fiber Type	Single-mode
Fiber Core Diameter	8.2 μ m
Fiber Category	OS2
Fiber Code	E
Performance Option Code	31
Wavelengths	1310 nm / 1383 nm / 1550 nm
Maximum Attenuation	0.65 dB/km / 0.65 dB/km / 0.5 dB/km
Serial 1 Gigabit Ethernet	5000 m / - / -
Serial 10 Gigabit Ethernet	10000 m / - / 40000 m

* ITU-T G.652 D compliant.

- Notes:
- 1) Improved attenuation and bandwidth options available.
 - 2) Bend-insensitive single-mode fibers available on request.
 - 3) Contact a Corning Cable Systems Customer Care Representative for additional information.

Ordering Information

Part Number	024E81-33131-24
Product Description	MIC [®] Tight-Buffered Cable, Riser, 24 F, Single-mode (OS2)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

