

# MIC® Tight-Buffered Cable, Plenum

2 F, 62.5 µm multimode (OM1)

CORNING

Corning Cable Systems MIC® Plenum Cables are designed for use in plenum, riser and general purpose environments for intrabuilding backbone and horizontal installations. These multifiber cables use 900 µm TBII® Buffered Fibers to allow easy, consistent stripping and to facilitate termination. The fibers are surrounded by dielectric strength members and protected by a flame-retardant outer jacket.

The all-dielectric cable construction requires no grounding or bonding. MIC Plenum cables are ideal for routing inside buildings, within plenum areas and riser shafts, to the telecommunications rooms and workstations. The MIC Plenum Cables meet the application requirements of the National Electrical Code® (NEC®) Article 770 and are OFNP and FT-6 listed.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

## Features and Benefits

### 900 µm TBII® Buffered Fibers

Easy, consistent stripping

### All-dielectric construction

Requires no grounding or bonding

### Flame-retardant jacket

Rugged and durable



## Standards

### Approval and Listings

National Electrical Code® (NEC®) OFNP, CSA FT-6, ICEA S-83-596

### Flame Resistance

NFPA 262 (for plenum, riser and general building applications)



# MIC<sup>®</sup> Tight-Buffered Cable, Plenum

2 F, 62.5 μm multimode (OM1)

CORNING

## Specifications

### General Specifications

Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser, Plenum
Cable Type	Tight-Buffered
Product Type	Distribution
Flame Rating	Plenum (OFNP)
Fiber Category	62.5 μm MM (OM1)

### Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	0 °C to 60 °C (32 °F to 140 °F)
Operation	0 °C to 70 °C (32 °F to 158 °F)

### Cable Design

Central Element	Yarn
Fiber Count	2
Tight Buffer Color	Blue, Orange
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Orange

### Mechanical Characteristics Cable

Max. Tensile Strengths, Short-Term	440 N (100 lbf)
Max. Tensile Strengths, Long-Term	132 N (30 lbf)
Nominal Outer Diameter	5 mm (0.2 in)
Weight	21 kg/km (15 lb/1000 ft)
Min. Bend Radius Installation	75 mm (3 in)
Min. Bend Radius Operation	25 mm (1 in)

# MIC<sup>®</sup> Tight-Buffered Cable, Plenum

2 F, 62.5 µm multimode (OM1)



## Fiber Specifications

Optical Characteristics (cabled)	
Fiber Core Diameter	62.5 µm
Fiber Type	Multimode
Fiber Category	OM1
Fiber Code	K
Performance Option Code	30
Wavelengths	850 nm / 1300 nm
Maximum Attenuation	3.4 dB/km / 1.0 dB/km
Min. Overfilled Launch (OFL) Bandwidth	200 MHz*km / 500 MHz*km
Minimum Effective Modal Bandwidth (EMB)	220 MHz*km / -
Serial 1 Gigabit Ethernet	300 m / 550 m
Serial 10 Gigabit Ethernet	33 m / -

Notes: 1) Improved attenuation and bandwidth options available.  
2) Bend-insensitive single-mode fibers available on request.  
3) Contact a Corning Cable Systems Customer Care Representative for additional information.

## Ordering Information

Part Number	002K88-31130-29
Product Description	MIC <sup>®</sup> Tight-Buffered Cable, Plenum, 2 F, 62.5 µm multimode (OM1)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

