

# MIC® DX Tight-Buffered Armored Cable, Plenum

24 F, 50 µm multimode (OM2)

CORNING

Corning Cable Systems MIC® DX Armored Plenum Cables are standard MIC subunits placed inside a dielectric armor for ruggedness and superior crush resistance without the conductive properties of traditional armor. These cables are designed for use in intrabuilding backbone and horizontal installations. Individually jacketed TBI® Buffered Fibers enable easy, consistent stripping and facilitate termination.

The fibers are stranded around a dielectric central member that is protected by a flexible, all-dielectric armor offering easy, one-step installation and over four times the crush protection of unarmored cables. With a flame-retardant outer jacket, this cable is particularly useful for heavy traffic or more challenging mechanical exposure conditions and applications requiring extra rugged cables.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

## Features and Benefits

### Dielectric armor

Four times crush protection compared to unarmored

### TBI® Buffered Fibers



Easy, consistent stripping

### Flame-retardant jacket

Rugged and durable

### Easy armor removal

Increased safety and speed at installation



## Standards

### Approval and Listings

National Electrical Code® (NEC®) OFNP, CSA FT-6, ICEA S-83-596

### Flame Resistance

NFPA 262 (for plenum, riser and general building applications)

# MIC<sup>®</sup> DX Tight-Buffered Armored Cable, Plenum

24 F, 50 µm multimode (OM2)

CORNING

## Specifications

General Specifications	
Environment	Indoor
Application	General Purpose Horizontal, Plenum
Cable Type	Tight-Buffered
Product Type	Dielectric armor
Flame Rating	Plenum (OFNP)
Fiber Category	50 µm MM (OM2)

Temperature Range	
Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	0 °C to 60 °C (32 °F to 140 °F)
Operation	0 °C to 70 °C (32 °F to 158 °F)

Cable Design	
Fiber Count	24
Tight Buffer Color	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Tight Buffer Color, Layer 2	Violet, Rose, Aqua, Blue*, Orange*, Green*, Brown*, Slate*, White*, Red*, Black*, Yellow*, Violet*, Rose*, Aqua*
Tensile Strength Elements and/or Armoring - Layer 2	Dielectric strength members
Inner Jacket Material	Flame-retardant
Tensile Strength Elements and/or Armoring - Layer 3	Dielectric armor
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Orange

Mechanical Characteristics Cable	
Nominal Inner Cable Diameter	6.8 mm (0.27 in)
Nominal Outer Diameter	13.1 mm (0.52 in)
Weight	188.7 kg/km (126.8 lb/1000 ft)
Max. Tensile Strengths, Short-Term	2600 N (585 lbf)
Max. Tensile Strengths, Long-Term	867 N (195 lbf)
Min. Bend Radius Installation	197 mm (7.7 in)
Min. Bend Radius Operation	131 mm (5.2 in)

# MIC<sup>®</sup> DX Tight-Buffered Armored Cable, Plenum

24 F, 50  $\mu$ m multimode (OM2)



## Fiber Specifications

Optical Characteristics (cabled)	
Fiber Type	Multimode
Fiber Core Diameter	50 $\mu$ m
Fiber Category	OM2
Fiber Code	T
Performance Option Code	31
Wavelengths	850 nm / 1300 nm
Maximum Attenuation	2.8 dB/km / 1 dB/km
Min. Overfilled Launch (OFL) Bandwidth	700 MHz*km / 500 MHz*km
Minimum Effective Modal Bandwidth (EMB)	950 MHz*km / -
Serial 1 Gigabit Ethernet	750 m / 600 m
Serial 10 Gigabit Ethernet	150 m / -

Notes: 1) 50  $\mu$ m multimode fiber macrobend loss  $\leq$  0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.  
2) Improved attenuation and bandwidth options available.  
3) Bend-insensitive single-mode fibers available on request.  
4) Contact a Corning Cable Systems Customer Care Representative for additional information.

## Ordering Information

Part Number	024T88-33131-D3
Product Description	MIC <sup>®</sup> DX Tight-Buffered Armored Cable, Plenum, 24 F, 50 $\mu$ m multimode (OM2)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

