


MIC® 250 Distribution Cable, Plenum

24 F, 50 µm multimode (OM3)

CORNING

Corning Cable Systems MIC® 250 Cables utilize 250 µm color-coded optical fibers, surrounded by dielectric strength members with a flexible, flame retardant outer jacket. These cables are ideal for creating multifiber preconnectorized assemblies as the 12-fiber groupings enable efficient compatibility with multifiber connectors. The flexible, flame-retardant jacket and non-preferential bend axis allow easy installation in space-constrained areas and the all-dielectric cable construction requires no grounding or bonding. The MIC 250 Cables meet the application requirements of the National Electrical Code® (NEC Article 770) and are OFNP and FT-6 listed for plenum, riser or general purpose applications.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.



Features and Benefits

Color-coded fibers


Quick and easy identification

12-fiber groupings

Compatibility with multifiber connectors

All-dielectric construction

Requires no grounding or bonding



Standards

Approval and Listings

National Electrical Code® (NEC®) OFNP, CSA FT-6, ICEA S-83-596

Flame Resistance

NFPA 262 (for plenum, riser and general building applications)

CORNING

MIC® 250 Distribution Cable, Plenum

24 F, 50 µm multimode (OM3)

CORNING

Specifications

General Specifications

Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser, Plenum
Cable Type	Loose Tube
Product Type	Distribution
Flame Rating	Plenum (OFNP)
Fiber Category	50 µm MM (OM3)

Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	0 °C to 60 °C (32 °F to 140 °F)
Operation	0 °C to 70 °C (32 °F to 158 °F)

Cable Design

Central Element	Yarn
Fiber Count	24
Fibers per Subunit	12
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Subunit Jacket Material	Flame-retardant
Subunit Color	Aqua
Number of Subunits	2
Number of Filling Elements	1
Number of Ripcords	1
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Aqua

Mechanical Characteristics Cable

Weight	69.3 kg/km (46.4 lb/1000 ft)
Nominal Outer Diameter	9.0 mm (0.35 in)
Max. Tensile Strengths, Short-Term	660 N (150 lbf)
Max. Tensile Strengths, Long-Term	200 N (45 lbf)

CORNING

MIC® 250 Distribution Cable, Plenum

24 F, 50 µm multimode (OM3)

CORNING

Mechanical Characteristics Cable

Min. Bend Radius Installation	135 mm (5.3 in)
Min. Bend Radius Operation	90 mm (3.5 in)

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Fiber Specifications

Optical Characteristics (cabled)

Fiber Type	Multimode
Fiber Core Diameter	50 µm
Fiber Category	OM3
Fiber Code	T
Performance Option Code	80
Wavelengths	850 nm / 1300 nm
Maximum Attenuation	3.0 dB/km / 1.0 dB/km
Min. Overfilled Launch (OFL) Bandwidth	1500 MHz*km / 500 MHz*km
Minimum Effective Modal Bandwidth (EMB)	2000 MHz*km / -
Serial 1 Gigabit Ethernet	1000 m / 600 m
Serial 10 Gigabit Ethernet	300 m / -

* Meets 0.75 ns optical skew when used in all Corning Cable Systems Plug & Play™/Pretium EDGE® Systems Solutions.

Notes: 1) 50 µm multimode fiber macrobend loss ≤ 0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.
2) Improved attenuation and bandwidth options available.
3) Bend-insensitive single-mode fibers available on request.
4) Contact a Corning Cable Systems Customer Care Representative for additional information.

Ordering Information

Part Number	024TD8-T1380-20
Product Description	MIC® 250 Distribution Cable, Plenum, 24 F, 50 µm multimode (OM3)

MIC[®] 250 Distribution Cable, Plenum

24 F, 50 µm multimode (OM3)

The Corning logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

Notes



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.