

Reel In A Box, MIC® Tight-Buffered Cable, Plenum


4 F, 50 µm multimode (OM2)

CORNING

Reel in a Box is Corning Cable Systems' innovative packaging solution for small reels of fiber optic cable in all inside plant applications, such as collocation data centers and wireless projects. This packaging solution provides features that enable our customers greater efficiencies than before.

Corning Cable Systems MIC® Plenum Cables are designed for use in plenum, riser and general purpose environments for intrabuilding backbone and horizontal installations. These multifiber cables use 900 µm TBII® Buffered Fibers to allow easy, consistent stripping and to facilitate termination. The fibers are surrounded by dielectric strength members and protected by a flame-retardant outer jacket.

The all-dielectric cable construction requires no grounding or bonding. MIC Plenum cables are ideal for routing inside buildings, within plenum areas and riser shafts, to the telecommunications rooms and workstations. The MIC Plenum Cables meet the application requirements of the National Electrical Code® (NEC®) Article 770 and are OFNP and FT-6 listed.




Standards

Approval and Listings

National Electrical Code® (NEC®) OFNP, CSA FT-6, ICEA S-83-596

Flame Resistance

NFPA 262 (for plenum, riser and general building applications)



Reel In A Box, MIC® Tight-Buffered Cable, Plenum

4 F, 50 µm multimode (OM2)

CORNING

Specifications

General Specifications

Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser, Plenum
Cable Type	Tight-Buffered
Product Type	Distribution
Flame Rating	Plenum (OFNP)
Fiber Category	50 µm MM (OM2)
Fiber Length	150 m (500 ft)

Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	0 °C to 60 °C (32 °F to 140 °F)
Operation	0 °C to 70 °C (32 °F to 158 °F)

Cable Design

Central Element	Yarn
Fiber Count	4
Tight Buffer Color	Blue, Orange, Green, Brown
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Orange

Mechanical Characteristics Cable

Max. Tensile Strengths, Short-Term	440 N (100 lbf)
Max. Tensile Strengths, Long-Term	132 N (30 lbf)
Nominal Outer Diameter	5.3 mm (0.21 in)
Weight	25 kg/km (17 lb/1000 ft)
Min. Bend Radius Installation	80 mm (3.2 in)
Min. Bend Radius Operation	27 mm (1.1 in)

Reel In A Box, MIC[®] Tight-Buffered Cable, Plenum

4 F, 50 µm multimode (OM2)

CORNING

Fiber Specifications

Optical Characteristics (cabled)	
Fiber Type	Multimode
Fiber Core Diameter	50 µm
Fiber Category	OM2
Fiber Code	T
Performance Option Code	31
Wavelengths	850 nm / 1300 nm
Maximum Attenuation	2.8 dB/km / 1 dB/km
Min. Overfilled Launch (OFL) Bandwidth	700 MHz*km / 500 MHz*km
Minimum Effective Modal Bandwidth (EMB)	950 MHz*km / -
Serial 1 Gigabit Ethernet	750 m / 600 m
Serial 10 Gigabit Ethernet	150 m / -

Notes: 1) 50 µm multimode fiber macrobend loss ≤ 0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.
2) Improved attenuation and bandwidth options available.
3) Bend-insensitive single-mode fibers available on request.
4) Contact a Corning Cable Systems Customer Care Representative for additional information.

Ordering Information

Part Number	004T88-31131-29
Product Description	Reel in a Box, MIC [®] Tight-Buffered Cable, Plenum, 4 F, 50 µm multimode (OM2)

Shipping Information

Packaging Method	Reel In A Box
Dimensions (HxWxD)	39.37 cm 39.37 cm 38.73 cm (15.5 in 15.5 in 15.25 in)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING