

MIC® DX Tight-Buffered Armored Cable, Riser

6 F, 50 µm multimode (OM3)

CORNING

Corning Cable Systems MIC® DX Armored Riser Cables are standard MIC subunits placed inside a dielectric armor for ruggedness and superior crush resistance without the conductive properties of traditional armor. These cables are designed for use in intrabuilding backbone and horizontal installations. Individually jacketed TBII® Buffered Fibers enable easy, consistent stripping and facilitate termination.

The fibers are stranded around a dielectric central member that is protected by a flexible, all-dielectric armor offering easy, one-step installation and over four times the crush protection of unarmored cables. With a flame-retardant outer jacket, this cable is particularly useful for heavy traffic or more challenging mechanical exposure conditions and applications requiring extra rugged cables.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

Features and Benefits

Dielectric armor

Four times crush protection compared to unarmored

TBII® Buffered Fibers

Easy, consistent stripping

Flame-retardant jacket

Rugged and durable

Easy armor removal

Increased safety and speed at installation



Standards

Approval and Listings

National Electrical Code®
(NEC®) OFNR, CSA FT-4,
ICEA S-83-596

Flame Resistance

UL-1666 (for riser and general building applications)



MIC® DX Tight-Buffered Armored Cable, Riser

6 F, 50 µm multimode (OM3)

CORNING

Specifications

General Specifications

Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser
Cable Type	Tight-Buffered
Product Type	Dielectric armor
Flame Rating	Riser (OFNR)
Fiber Category	50 µm MM (OM3)

Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-20 °C to 70 °C (-4 °F to 158 °F)

Cable Design

Fiber Count	6
Tight Buffer Color	Blue, Orange, Green, Brown, Slate, White
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Inner Jacket Material	Flame-retardant
Tensile Strength Elements and/or Armoring - Layer 3	Dielectric armor
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Aqua

Mechanical Characteristics Cable

Nominal Inner Cable Diameter	5.5 mm (0.22 in)
Nominal Outer Diameter	10.1 mm (0.4 in)
Weight	94.1 kg/km (63.2 lb/1000 ft)
Max. Tensile Strengths, Short-Term	890 N (200 lbf)
Max. Tensile Strengths, Long-Term	444 N (100 lbf)
Min. Bend Radius Installation	152 mm (6 in)
Min. Bend Radius Operation	101 mm (4 in)

CORNING

MIC® DX Tight-Buffered Armored Cable, Riser

6 F, 50 µm multimode (OM3)

CORNING

Fiber Specifications

Optical Characteristics (cabled)	
Fiber Type	Multimode
Fiber Core Diameter	50 µm
Fiber Category	OM3
Fiber Code	T
Performance Option Code	80
Wavelengths	850 nm / 1300 nm
Maximum Attenuation	2.8 dB/km / 1 dB/km
Min. Overfilled Launch (OFL) Bandwidth	1500 MHz*km / 500 MHz*km
Minimum Effective Modal Bandwidth (EMB)	2000 MHz*km / -
Serial 1 Gigabit Ethernet	1000 m / 600 m
Serial 10 Gigabit Ethernet	300 m / -
Induced Attenuation @ 7.5 mm Radius	< 30 dB up to 80 dB

* Meets 0.75 ns optical skew when used in all Corning Cable Systems Plug & Play™/Pretium EDGE® Systems Solutions.

Notes: 1) 50 µm multimode fiber macrobend loss ≤ 0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.
2) Improved attenuation and bandwidth options available.
3) Bend-insensitive single-mode fibers available on request.
4) Contact a Corning Cable Systems Customer Care Representative for additional information.

Ordering Information

Part Number	006T81-31180-D1
Product Description	MIC® DX Tight-Buffered Armored Cable, Riser, 6 F, 50 µm multimode (OM3)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.
Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING