# MIC<sup>®</sup> DX Tight-Buffered Armored Cable, Plenum

12 F, 50 µm multimode (OM4)

### CORNING

Corning Cable Systems MIC<sup>®</sup> DX Armored Plenum Cables are standard MIC subunits placed inside a dielectric armor for ruggedness and superior crush resistance without the conductive properties of traditional armor. These cables are designed for use in intrabuilding backbone and horizontal installations. Individually jacketed TBII<sup>®</sup> Buffered Fibers enable easy, consistent stripping and facilitate termination.

The fibers are stranded around a dielectric central member that is protected by a flexible, all-dielectric armor offering easy, one-step installation and over four times the crush protection of unarmored cables. With a flame -retardant outer jacket, this cable is particularly useful for heavy traffic or more challenging mechanical exposure conditions and applications requiring extra rugged cables.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

#### **Features and Benefits**

**Dielectric armor** Four times crush protection compared to unarmored

TBII<sup>®</sup> Buffered Fibers Easy, consistent stripping


Flame-retardant jacket Rugged and durable

Easy armor removal Increased safety and speed at installation

### Standards

Approval and Listings	National Electrical Code <sup>®</sup> (NEC <sup>®</sup> ) OFNP, CSA FT-6, ICEA S-83-596
Flame Resistance	NFPA 262 (for plenum, riser and general building appli- cations)





# CORNING

# MIC<sup>®</sup> DX Tight-Buffered Armored Cable, Plenum

12 F, 50 µm multimode (OM4)

# CORNING

-p------

General Specifications	
Environment	Indoor
Application	General Purpose Horizontal, Plenum
Cable Type	Tight-Buffered
Product Type	Dielectric armor
Flame Rating	Plenum (OFNP)
Fiber Category	50 µm MM (OM4)

Temperature Range	
Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	0 °C to 60 °C (32 °F to 140 °F)
Operation	0 °C to 70 °C (32 °F to 158 °F)

Cable Design	
Fiber Count	12
Tight Buffer Color	Blue, Orange, Green
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Tight Buffer Color, Layer 2	Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Tensile Strength Elements and/or Armoring - Layer 2	Dielectric strength members
Inner Jacket Material	Flame-retardant
Tensile Strength Elements and/or Armoring - Layer 3	Dielectric armor
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Aqua

Mechanical Characteristics Cable		
Nominal Inner Cable Diameter	5.6 mm (0.22 in)	
Nominal Outer Diameter	11.5 mm (0.45 in)	
Weight	143.3 kg/km (96.3 lb/1000 ft)	
Max. Tensile Strengths, Short-Term	1000 N (225 lbf)	
Max. Tensile Strengths, Long-Term	593 N (133 lbf)	
Min. Bend Radius Installation	173 mm (6.8 in)	
Min. Bend Radius Operation	115 mm (4.5 in)	



# MIC<sup>®</sup> DX Tight-Buffered Armored Cable, Plenum

12 F, 50 µm multimode (OM4)

# CORNING

#### **Fiber Specifications**

Optical Characteristics (cabled)		
Fiber Type	Multimode	
Fiber Core Diameter	50 μm	
Fiber Category	OM4	
Fiber Code	Т	
Performance Option Code	90	
Wavelengths	850 nm / 1300 nm	
Maximum Attenuation	2.8 dB/km / 1 dB/km	
Min. Overfilled Launch (OFL) Bandwidth	3500 MHz*km / 500 MHz*km	
Minimum Effective Modal Bandwidth (EMB)	4700 MHz*km / -	
Serial 1 Gigabit Ethernet	1100 m / 600 m	
Serial 10 Gigabit Ethernet	550 m / -	

\* Assumes 1.0 dB maximum total connector/splice loss.

\* Meets 0.75 ns optical skew when used in all Corning Cable Systems Plug & Play™/Pretium EDGE® Systems Solutions.

Notes: 1) 50  $\mu$ m multimode fiber macrobend loss  $\leq$  0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.

2) Improved attenuation and bandwidth options available.

3) Bend-insensitive single-mode fibers available on request.

4) Contact a Corning Cable Systems Customer Care Representative for additional information.

# **Ordering Information**

Part Number	012T88-33190-D3
Product Description	$MIC^{\circledast}$ DX Tight-Buffered Armored Cable, Plenum, 12 F, 50 $\mu m$ multimode (OM4)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks. Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

