


MIC® Unitized Tight-Buffered, Interlocking Armored Cable, Riser

96 F, Single-mode (OS2)

CORNING

Corning Cable Systems MIC® Interlocking Armored Riser Cables are designed for use in intrabuilding backbone and horizontal installations. They use individually jacketed TBII® Buffered Fibers enabling easy, consistent stripping and facilitating termination. The fibers are grouped into jacketed subunits and surrounded by a dielectric central member. The core is protected by a flexible, spirally wrapped, aluminum interlocking armor that offers easy, one-step installation and over seven times the crush protection of unarmored cables. With a flame-retardant outer jacket, this cable is particularly useful for heavy traffic or more challenging mechanical exposure conditions and applications requiring extra rugged cables.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.



Part Number: 096E81-T3131-A1

Features and Benefits

Flexible, interlocking armor design

Seven times crush protection compared to unarmored cables

TBII® Buffered Fibers


Easy, consistent stripping

6- or 12-fiber jacketed subunits

Quick and easy identification

Flame-retardant jacket

Rugged and durable



Cross Section of Part Number: 096E81-T3131-A1

Standards

Approval and Listings

National Electrical Code®
(NEC®) OFCR, CSA FT-4,
ICEA S-83-596

Flame Resistance

UL-1666 (for riser and general building applications)

CORNING

MIC[®] Unitized Tight-Buffered, Interlocking Armored Cable, Riser

96 F, Single-mode (OS2)

CORNING

Specifications

General Specifications

Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser
Cable Type	Tight-Buffered
Product Type	Interlocking armor
Flame Rating	Riser (OFCR)
Fiber Category	Single-mode (OS2)

Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-20 °C to 70 °C (-4 °F to 158 °F)

Cable Design

Central Element	Jacketed GRP
Fiber Count	96
Subunit Central Element	Dielectric
Fibers per Subunit	12
Tight buffer color subunit	Blue, Orange, Green, Brown, Slate, White
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Tight Buffer Color Subunit, Layer 2	Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Tensile Strength Elements and/or Armoring - Layer 2	Dielectric strength members
Subunit Color	Yellow
Number of Subunits	8
Number of Ripcords	19
Inner Jacket Material	Flame-retardant
Tensile Strength Elements and/or Armoring - Layer 3	Interlocking armor
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Yellow

Mechanical Characteristics Cable

Max. Tensile Strengths, Short-Term	1320 N (300 lbf)
Max. Tensile Strengths, Long-Term	400 N (90 lbf)
Nominal Inner Cable Diameter	22.2 mm (0.86 in)

CORNING

MIC[®] Unitized Tight-Buffered, Interlocking Armored Cable, Riser

96 F, Single-mode (OS2)

CORNING

Mechanical Characteristics Cable

Nominal Outer Diameter	31.2 mm (1.23 in)
Weight	732 kg/km (491 lb/1000 ft)
Min. Bend Radius Installation	468 mm (18.4 in)
Min. Bend Radius Operation	312 mm (12.2 in)

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Fiber Specifications

Optical Characteristics (cabled)

Fiber Type	Single-mode
Fiber Core Diameter	8.2 μ m
Fiber Category	OS2
Fiber Code	E
Performance Option Code	31
Wavelengths	1310 nm / 1383 nm / 1550 nm
Maximum Attenuation	0.65 dB/km / 0.65 dB/km / 0.5 dB/km
Serial 1 Gigabit Ethernet	5000 m / - / -
Serial 10 Gigabit Ethernet	10000 m / - / 40000 m

* ITU-T G.652 D compliant.

Notes: 1) Improved attenuation and bandwidth options available.
2) Bend-insensitive single-mode fibers available on request.
3) Contact a Corning Cable Systems Customer Care Representative for additional information.

Ordering Information

Part Number	096E81-T3131-A1
Product Description	MIC [®] Unitized Tight-Buffered, Interlocking Armored Cable, Riser, 96 F, Single-mode (OS2)

CORNING

MIC[®] Unitized Tight-Buffered, Interlocking Armored Cable, Riser

96 F, Single-mode (OS2)

The Corning logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

Notes



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.
Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

The Corning logo consists of the word "CORNING" in a large, bold, sans-serif font.